

Composite and S-Video to DVI-D Video Converter with Scaler

Produkt ID: VID2DVIDTV



This Composite video/S-Video to DVI-D Video Converter/Scaler lets you convert from composite/s-video/YCbCr/RGB resolutions and video formats to DVI-D, automatically detecting the video source input resolution and allowing you to customize the output resolution and refresh rate through an easy to use on-screen-display menu.

Great for home theatre peripherals like DVD players, the Composite video/S-Video to DVI-D Video Converter/Scaler lets you connect non-DVI/HDTV enabled equipment to DVI or HDTV display devices like flat panel monitors, DVI projectors and plasma screen TVs.

Certifikat, rapporter och kompatibilitet

Användning

- Security
- Display video feeds from DVD players, VCRs and more on DVI monitors, plasma displays, DVI input projectors and HDTVs
- Home Theatre
- Educational
- Medical
- Conference Room

Funktioner

- Adjust picture brightness, contrast, color, and RGB levels
- Compatible with input from broadcast formats worldwide, including NTSC and PAL
- A 48 MByte frame buffer eliminates image tear/video hiccupping
- Includes a memory recall feature that automatically reinstates the setting last used
- Includes a plastic bracket for wall mounts or side panel installation

Hårdvara

Garantipolicy	2 Years
Active or Passive Adapter	Aktiv
AV-ingång	Composite S-Video Component
AV-utgång	DVI
Audio	Nej

Prestanda

Stödda upplösningar	HDTV Output(50/60Hz) 1080i, 720p, 576p, 480p PC Output (RGBHV, Progressive Scan) 1280 x 1024, 1280 x 768, 1024 x 768, 800 x 600, 640 x 480
Signalnivåer	Input Signal Levels: Video @ 1V p-p, 75 ohm Y @ 1 V p-p, 75 ohm Color @ 0.7V p-p, 75 ohm

Kontakt(er)

Connector A	Kompositvideo (1 x RCA)
-------------	-------------------------

S-Video (4-stifts, Mini-DIN)

Connector B

DVI-I (29-stifts)

Särskilda
anmärkningar/krav

Obs.

Multiple refresh rates supported on PC output - See product manual for full list

Ström

Power Source

AC-adapter medföljer

Inspänning

100 - 240 AC

Utspänning

5 DC

Utström

2.6A

Polaritet på mittpol

Positiv

Strömförbrukning

13

Utseende

Färg

Svart

Produktlängd

5.7 in [14.6 cm]

Produktbredd

3.0 in [77 mm]

Produkt höjd

1.2 in [30 mm]

Produktvikt

9.9 oz [280 g]

Förpackning

Package Length

11.1 in [28.3 cm]

Package Width

2.8 in [72 mm]

Package Height

7.3 in [18.6 cm]

Fraktvikt (förpackning)

2.4 lb [1.1 kg]

Vad det är i lådan

Ingår i paketet

Video to DVI/HDTV Scaler

Plastic Bracket



3 foot (1 meter) Composite RCA cable

YCbCr RCA to 8 pin DIN adapter

6 foot (1.8 meter) DVI-D DVI cable M-M

Wall-mount power adapter

User's manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

