

## Composite and S-Video to HDMI Converter with Audio

Product ID: VID2HDCON



The VID2HDCON Composite and S-Video to HDMI Video Converter (with Audio) lets you connect an S-Video or Composite device, along with supporting 3.5mm audio, to your HDMI monitor or television.

Equipped with convenient selector switches for easy configuration, the S-Video/Composite to HDMI converter is able to function with both NTSC and PAL systems, and offers support for output resolutions up to 1600x1200 (PC) or 1080p (TV) to seamlessly integrate with almost any display.

The converter features an integrated 3.5mm audio connection that enables sending the output through a single HDMI cable to your destination display, avoiding the hassle of running a separate audio cable.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Convert VCRs, DVD players, camcorders, video game consoles and other home theater devices to work on HDMI displays

### Features

- Functions with NTSC and PAL systems
- PC/TV resolution selector switch for compatibility with many different displays
- Advance 3D motion adaptive de-interlace
- 50/60 Hz frame rate conversion

- On Screen Display
- Plug and play installation - no software/drivers required
- 3D (frame based) motion adaptive YNR/CNR noise reduction

<b>Hardware</b>	Warranty	2 Years
	Active or Passive Adapter	Active
	AV Input	Composite
	AV Input	S-Video
	AV Input	3.5 mm Stereo Audio
	AV Output	HDMI
	Audio	Yes
	Industry Standards	NTSC 3.58 and PAL
<b>Performance</b>	Supported Resolutions	PC - 1600x1200, 1280x1024, 1024x768 TV - 1080p, 720p, 576p, 480p
<b>Connector(s)</b>	Connector Type(s)	Composite Video (1 x RCA)
	Connector Type(s)	S-Video (4 pin, Mini-DIN)
	Connector Type(s)	HDMI (19 pin)
	Connector Type(s)	3.5 mm Mini-Jack (3 Position)
<b>Indicators</b>	LED Indicators	Red - S-Video, Yellow - Composite Video
<b>Power</b>	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.3A
	Output Voltage	5 DC
	Output Current	1.2A
	Center Tip Polarity	Positive
	Plug Type	M
	Power Consumption (In Watts)	2.5
<b>Environmental</b>	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	20~90% RH

<b>Physical Characteristics</b>	Color	Black
	Material	Plastic
	Product Length	6.5 in [1.6 cm]
	Product Width	6.4 in [1.6 cm]
	Product Height	1.3 in [33.5 mm]
	Weight of Product	2.8 oz [79 g]
<b>Packaging Information</b>	Package Length	4.9 in [1.2 cm]
	Package Width	6.1 in [1.6 cm]
	Package Height	2.2 in [56 mm]
	Shipping (Package) Weight	10.9 oz [310 g]
<b>What's in the Box</b>	Included in Package	Composite/S-Video to HDMI Converter
	Included in Package	Universal Power Adapter (NA/JP, EU, UK, ANZ)
	Included in Package	Instruction Manual

***\*Product appearance and specifications are subject to change without notice.***

