

Composite and S-Video to VGA Video Converter

Produkt ID: VID2VGATV



This Composite/S-Video to VGA video converter scales and converts composite video, s-video, and YCbCr (RGB) video to VGA/HDTV – a simple solution for connecting non-VGA/HDTV enabled equipment to VGA or HDTV display devices like CRT monitors, VGA projectors, LCD displays and plasma displays.

The video converter automatically detects your source's input resolution and allows you to customize its output resolution and refresh rate through an easy to use on-screen-display menu – providing a convenient, easy-to-use way to get the most from your HD display.

Certifikat, rapporter och kompatibilitet

Användning

- Display video feeds from DVD players on VGA input projectors and HDTV sets
- Monitor Security cameras with s-video or composite signaling using VGA monitors or televisions
- Adapt VHS tapes in the classroom to show videos on newer televisions
- Convert legacy Medical imaging equipment to display on computer monitors
- Use in the Conference Room to adapt legacy video equipment and connect to newer projectors

Funktioner

- Adjust picture brightness, contrast, color, RGB level and horizontal/vertical positioning
- Includes a plastic bracket for wall mounts or side panel installation
- Output is analog RGBHV or YPbPr via the HD-15 VGA connector
- Compatible with input from broadcast formats worldwide, including NTSC and PAL
- A 48 MByte frame buffer eliminates image tear/video hiccups
- Includes a memory recall feature that automatically reinstates the setting last used

Hårdvara

Garantipolicy	2 Years
Active or Passive Adapter	Aktiv
AV-ingång	Composite S-Video Component
AV-utgång	VGA Component
Audio	Nej

Prestanda

Stödda upplösningar	PC Output (RGBHV, progressive scan) 640 x 480, 800 x 600, 1024 x 768, 1280 x 768, 1280 x 1024 HDTV (50/60Hz, YPbPr/RGBHV) 480p, 576p, 720p, 1080i
Signalnivåer	Input Video @ 1V p-p, 75 ohm Y @ 1 V p-p, 75 ohm Color @ 0.7V p-p, 75 ohm

Kontakt(er)

Connector A	Kompositvideo (1 x RCA)
	S-Video (4-stifts, Mini-DIN)
	Komponentvideo (3 x RCA)
Connector B	VGA (15-stifts, High Density D-Sub)

Särskilda
anmärkningar/krav

Obs.	Multiple refresh rates supported on PC output - See product manual for full list
------	--

Ström

Power Source	AC-adapter medföljer
Utspänning	5 DC
Utström	2.6A
Polaritet på mittpol	Positiv
Strömförbrukning	13

Miljö

Drifttemperatur	0°C to 40°C (32°F to 104°F)
Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
Luftfuktighet	20 - 90% (non-condensing)

Utseende

Färg	Svart
Produktlängd	5.7 in [14.6 cm]
Produktbredd	3.0 in [77.0 mm]
Produkt höjd	1.2 in [30.0 mm]
Produktvikt	8.5 oz [240.0 g]

Förpackning

Package Length	9.9 in [25.2 cm]
----------------	------------------



Package Width	2.4 in [62.0 mm]
Package Height	5.4 in [13.8 cm]
Fraktvikt (förpackning)	31.4 oz [890.0 g]

Vad det är i lådan

Ingår i paketet	Video to HDTV/VGA Scaler
	Plastic Bracket
	4ft (1.2m) S-Video cable
	3ft (1m) VGA to YPbPr M/M
	3ft (1m) Composite RCA Cable
	YCbCr RCA to 8 pin DIN adapter
	4ft (1.2m) VGA cable M-M
	Universal Power Adapter (US/UK/EU/AUS)
	User Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

