

Video Wall Mount - Pop-Out Design - Micro-Adjustment

Product ID: VIDWALLMNT



This professional video-wall mount features an innovative pop-out design that enables fast and easy display alignment and adjustment, within a multi-display video wall.

Engineered with heavy-duty steel, the video-wall mount securely supports 45" to 70" displays, weighing up to 154 lb. (70 kg).

Using multiple VIDWALLMNT wall mounts, you can create an impressive video wall, enabling you to align your displays in unison. It's the ideal solution for public, business and commercial displays and includes a theft deterrence feature (padlock required).

With its unique pop-out design, the video wall mount helps you align your displays with perfect precision. Once installed, you simply press gently on the front of the display and the mount extends out from the wall for rear-screen access. This pop-out feature makes it easy to adjust the position and angle of the display, or replace a display when required.

The video-wall mount features 6 points of micro-adjustment, with vertical, tilt and swivel adjustments, to provide exact display alignment and an optimum viewing angle. You can tilt your display +3 / -5 degrees, adjust the swivel angle +1.2 / - 1.2 degrees, and rotate the display +3 / - 3 degrees. The video-wall mount also features lateral shift brackets, making it easy to move the display to the left or right for ideal alignment in your video wall.

This video-wall mounting system is designed for easy set-up and maintenance. The pop-out design also assists in installation and maintenance, plus a convenient kickstand allows you to tilt the display up to 12 degrees giving you extra room when adjusting cables or accessing ports.

The VIDWALLMNT is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Create a video wall in a lobby, retail venue or commercial space
- Set up multiple screens for presentations
- Ideal in educational facilities, medical or conference centers

Features


- Create an impressive video wall with this flat-screen TV mount, supporting a 45" to 70" display (theft deterrent design)
- Heavy-duty steel construction supports displays up to 154 lb. (70 kg)
- Pop-out design extends up to 12" (306 mm) to give rear-screen access for display adjustment
- 6 points of micro-adjustment (vertical, tilt and swivel) for exact display alignment
- Lateral shift brackets to adjust monitors, left or right, and swivel angle of +1.2 / -1.2 degrees for precise alignment

Hardware

Warranty	5 Years
# of Displays Supported	1
Mounting Options	Wall-Mount
Minimum Profile from Wall	5.6 in [14.3 cm]
VESA Hole Pattern(s)	200x200 mm
	300x300 mm
	400x200 mm
	400x400 mm
	600x400 mm
	600x300 mm
	600X200 mm

Performance

Weight Capacity (Per Display)	154.7 lb [70 kg]
-------------------------------	------------------



Minimum Display Size	45"
Maximum Display Size	70"
Video Wall	Yes
Maximum Arm Extension	12.0 in [30.6 cm]
Display Tilt	+3 / -5
Anti-theft	Yes

Special Notes / Requirements

Note	The video-wall mount is designed for precise display alignment. You can tilt your display +3 / -5, adjust the swivel angle +1.2 / - 1.2, and rotate the display +3 / - 3.
------	---

Physical Characteristics

Color	Black
Material	Steel
Product Length	36.8 in [93.4 cm]
Product Width	12.0 in [30.6 cm]
Product Height	19.0 in [48.3 cm]
Weight of Product	29.8 lb [13.5 kg]

Packaging Information

Package Length	3.3 ft [1.0 m]
Package Width	20.1 in [51.0 cm]
Package Height	8.2 in [20.9 cm]
Shipping (Package) Weight	36.3 lb [16.4 kg]

What's in the Box

Included in Package	wall plate
	adjustment module
	adapter brackets



stoppers

plastic tabs

hex key

M5x14 mm screws

M6x14 mm screws

M8x20 mm screws

M6x30 mm screws

M8x30 mm screws

rectangular washers

small spacers

large spacers

6.3x55 mm screws

concrete anchors

washers

instruction manual

****Product appearance and specifications are subject to change without notice.***

