

2 Port DisplayPort Video Switch with Audio & IR Remote Control

Produkt ID: VS221DP



The VS221DP 2 Port DisplayPort Video Switch with Audio & IR Remote Control offers a reliable solution for switching between multiple DisplayPort audio/video sources for demanding high-resolution applications.

Supporting a native display resolution of 2560x1600 and 7.1 channel audio (when connected to supporting displays and sources), this simple, yet comprehensive DisplayPort A/V Switch features both push-button and infrared remote control source selection, and offers a compact form factor design.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- High resolution digital images in education in the classroom, lecture halls, and conference rooms with multiple sources to one DisplayPort monitor
- Multimedia design, multimedia post-production and video editing
- High resolution digital signage requiring multiple sources with one display
- High resolution medical imaging and Health care display, such as MRI and X-Ray display

Funktioner

- Supports resolutions up to 2560 x 1600 @ 60Hz, beyond 1080p
- 7.1 Channel High Definition Audio pass-through (with displays and sources that support DisplayPort audio)
- Supports native DisplayPort computer connections - no adapter required
- Supports DisplayPort ++ for use with VGA, DVI, or HDMI displays (please see accessories)
- Supports DDC2B monitor detection
- DisplayPort 1.1 Compliant

Hårdvara

Garantipolicy	2 Years
AV-ingång	DisplayPort
Portar	2
AV-utgång	DisplayPort
Audio	Ja
Hyllmonterbar	Valfri
Industristandarder	DisplayPort 1.1, EDID

Prestanda

Maximalt avstånd	10 m / 33 ft
Maximal digital upplösning	2560x1600 @ 60Hz
Stöd för widescreen	Ja

Kontakt(er)

Connector A	DisplayPort (20-stifts)
Connector B	DisplayPort (20-stifts)

Särskilda anmärkningar/krav

Obs.	Audio support requires source (PC) and display to both support audio pass through
------	---

Indikatorer

LED-indikatorer	Green - Online and Display indicator (One LED per port)
-----------------	---

Ström

Power Source	AC-adapter medföljer
Inspänning	110V-240V AC
Inström	0.5A
Utspänning	5 DC
Utström	2A
Polaritet på mittpol	Positiv
Kontakttyp	M
Strömförbrukning	10

Miljö

Drifttemperatur	0°C to 40°C (32°F to 104°F)
Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
Luftfuktighet	0~80% RH

Utseende

Färg	Svart
Kabinetttyp	Aluminium
Produktlängd	5.2 in [13.1 cm]
Produktbredd	2.6 in [65 mm]
Produkt höjd	1.0 in [26 mm]
Produktvikt	17.6 oz [500 g]

Förpackning

Package Length	10.6 in [27 cm]
Package Width	7.3 in [18.6 cm]
Package Height	3.1 in [80 mm]



Fraktvikt
(förpackning) 21.2 oz [600.0 g]

Vad det är i
lådan

Ingår i paketet	2 Port DisplayPort Switch
	IR Remote Control
	Universal Power Adapter (US/UK/EU/AUS)
	Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

