

## 2 Port HDMI Switch w/ Automatic and Priority Switching - 1080p

Product ID: VS221HDQ



Save time and hassle by automatically switching between your HDMI audio/video sources, using the VS221HDQ 2-Port HDMI Auto Switcher. This easy-to-use HDMI switch ensures seamless transition while switching video sources, with EDID copy maintaining your video resolution.

Ensure seamless transition while switching video sources, with EDID copy maintaining native resolution with support for 1080p. Video connection emulation ensures the settings on any connected computers are not disrupted while switching to a different video source.

Save time by connecting two HDMI video source devices to your HDMI display instead of manually connecting individual cables. Mounting hardware is also included for a tidy, professional installation.

Enjoy hassle-free operation with three different switching modes:

: Enables your most recently activated video source to be displayed automatically.

: Prioritizes input number two above input number one. If the video source connected to input number two is activated that source will be displayed.

: Enables you to manually select your HDMI source with easy-to-use front panel buttons.

This product is TAA compliant and backed by a Startech.com 2 warranty with lifetime technical support

### Certifications, Reports and Compatibility



### Applications

- Automatically switch between your Blu-ray player, set top box, or gaming console in a home theatre environment
- Connect and switch between two video sources on a test bench, for troubleshooting computers
- Switch between different video sources on your digital signage display in hospitals, shopping centers, or schools

## Features

- Auto switching
- Mounting hardware included
- Priority switching
- EDID emulation
- Built-in manual control console
- Video connection emulation
- Support for video resolution up to 1080p

<b>Hardware</b>	Warranty	2 Years
	AV Input	HDMI
	Ports	2
	AV Output	HDMI
	Cabling	HDMI
	Audio	Yes
	Rack-Mountable	Yes
<b>Performance</b>	Max Distance	10 m / 33 ft
	Maximum Digital Resolutions	1920x1200 / 1080p 1920x1200
	Supported Resolutions	1920x1080 (1080p)
	Audio Specifications	1280x720 (720p) 7.1 surround sound
<b>Connector(s)</b>	Connector A	HDMI (19 pin)
	Connector B	HDMI (19 pin)
<b>Indicators</b>	LED Indicators	Source #1 activated
	LED Indicators	Source #2 activated
<b>Power</b>	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.6 A

Output Voltage	12V DC
Output Current	1.5 A
Plug Type	M
Power Consumption (In Watts)	18

---

<b>Environmental</b>	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	0%~80%

---

<b>Physical Characteristics</b>	Color	Black
	Material	Aluminum and Plastic
	Product Length	6.1 in [1.6 cm]
	Product Width	2.6 in [65 mm]
	Product Height	0.8 in [20 mm]
	Weight of Product	10.2 oz [290 g]

---

<b>Packaging Information</b>	Package Length	11.6 in [2.9 cm]
	Package Width	7.8 in [2.0 cm]
	Package Height	2.8 in [72 mm]
	Shipping (Package) Weight	30.1 oz [853 g]

---

<b>What's in the Box</b>	Included in Package	HDMI auto switch
	Included in Package	instruction Manual
	Included in Package	universal power adapter (NA, EU, UK, AU)
	Included in Package	remote control
	Included in Package	mounting kit
	Included in Package	foot pad set

---

***\*Product appearance and specifications are subject to change without notice.***

