

2x2 HDMI Matrix Switch - 4K with Fast Switching and Auto-Sensing

Product ID: VS222HD4K



Save time and hassle by automatically switching between your HDMI audio/video sources. This 2x2 HDMI matrix switcher provides the ultimate viewing experience, with support for Ultra HD 4K. It lets you connect two HDMI sources to two HDMI displays, with exceptional 4K resolution, while switching seamlessly between your video sources.

The matrix switch supports Ultra HD 4K picture quality on two monitors while switching between content from HDMI source devices - including Blu-ray players or DVD players, computer systems, video game consoles, digital cable or satellite boxes, and A/V receivers.

4K support ensures a higher level of image clarity and visibility, delivering four times the resolution of 1080p - 8.29 million pixels versus 2.07 million pixels. It provides a more engaging visual experience for audiences in a wide range of venues including conference centers, boardrooms, educational facilities, and commercial settings. With its exceptional image quality, 4K resolution is also ideal for bringing your digital signage to life.

Enjoy hassle-free operation with four different switching modes:

- lets you route either HDMI source (Input 1 or Input 2) to either monitor (Output 1 and/or Output 2) - and independently switch two displays between two video sources.
- ensures minimal time for switching between HDMI sources. The switch provides effortless operation with advanced auto-sensing - it detects the latest connected HDMI source and automatically switches both outputs to that device. It also ensures no downtime in a digital signage application if a source signal is accidentally powered off or fails.
- identifies the first port to have first priority for HDMI sources, which will be output on both displays.
- enables you to manually select your HDMI source with front-panel buttons that are easy to use.

An IR remote control is included in the box, enabling you to select your desired input source remotely. The RS-232 serial control interface ensures easy remote operation with serial control enabled devices.

The matrix switch is easy to install. EDID emulation saves you time during setup by ensuring all of your display settings, such as native resolution and refresh rate, are communicated between your display and video source devices. The built-in EDID copy feature maximizes compatibility with your 4K display, to ensure a convenient plug-and-play installation and the sharpest image quality.

The VS222HD4K is TAA compliant and backed by a 2-year StarTech.com warranty with free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Run Ultra HD 4K multimedia presentations on two monitors in conference rooms, commercial settings or at trade shows
- Switch between different video sources on your digital signage displays in hospitals, shopping centers, or schools
- Connect and switch between two video sources and two displays on a test bench, for troubleshooting computers
- Automatically switch between your Blu-ray player, set-top box, or gaming console in a home theatre environment

Features

- Impressive image quality with support for Ultra HD 4K
- Easy operation with automatic, priority and manual switching between HDMI sources
- Access two HDMI source devices on two independent HDMI displays, with 2 x 2 matrix switching
- IR remote control included
- RS-232 serial control interface
- EDID copy support ensures accurate display output
- Backward compatible with high-definition 1080p
- Mounting hardware included

Hardware	Warranty	2 Years
	AV Input	HDMI
	Ports	2
	AV Output	HDMI
	Audio	Yes
	Industry Standards	HDMI 1.4
Performance	Maximum Cable Length	32.8 ft [10 m]
	Max Distance	10 m / 33 ft
	Maximum Digital Resolutions	4K @ 30 Hz
	Supported Resolutions	3840x2160 (4K)
	Wide Screen Supported	2560x1600
	Audio Specifications	1920x1200
		1920x1080 (1080p)

1280x720 (720p)

Yes

7.1 Surround sound

Connector(s)	Connector A	HDMI (19 pin)
	Connector B	HDMI (19 pin)
	Connector B	RJ-11
Indicators	LED Indicators	Active port LED
	LED Indicators	Power LED
Power	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Output Voltage	12V DC
	Output Current	1.5
	Power Consumption (In Watts)	18
Environmental	Operating Temperature	0C to 50C (32F to 122F)
	Storage Temperature	-20C to 70C (-4F to 158F)
	Humidity	0% ~ 80%
Physical Characteristics	Color	Black
	Product Length	6.1 in [1.6 cm]
	Product Width	2.6 in [65.000 mm]
	Product Height	0.8 in [20.000 mm]
	Weight of Product	10.4 oz [296.000 g]
Packaging Information	Package Length	6.1 in [1.6 cm]
	Package Width	9.3 in [2.4 cm]
	Package Height	2.6 in [65.000 mm]
	Shipping (Package) Weight	29.7 oz [841.000 g]
What's in the Box	Included in Package	2x2 HDMI matrix switch
	Included in Package	remote control

Included in Package	universal power adapter (NA/EU/UK/AU)
Included in Package	RJ11 cable (1200mm)
Included in Package	RJ11 to DB-9 serial adapter
Included in Package	quick start guide
Included in Package	mounting kit

****Product appearance and specifications are subject to change without notice.***

