

4 Port VGA Video Audio Switch with RS232 control

Produkt ID: VS410RVGAA



The VS410RVGAA 4 Port VGA Video Audio Switch with RS232 control lets you switch between four separate VGA signals, as well as the corresponding audio, for output to a single display or projector at resolutions up to 1920x1200 (PC) or 1080p (HDTV).

An ideal solution for situations where VGA and audio input ports are scarce, the VGA switch eliminates the hassle of having to swap out connections to your display and audio receiver, while letting you select the video source quickly and easily at the push of a button.

The VGA switch also features convenient remote switching capabilities through either RS232 serial remote control, or the included IR remote control - allowing you to switch between VGA input signals from a distance and in turn providing a convenient addition to presentation displays, trade shows, security environments and more.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Perfect for use in boardroom settings to let visitors connect to your display or projector
- Great for use in presentations, trade shows, conferences, retail, and entertainment applications
- Excellent solution for connecting and switching between multiple PC/HDTV's to one display

Funktioner

- Supports resolutions up to 1920x1200 (1080p)
- Supports VGA Video bandwidth of 650 MHz
- Includes an easy-to-use remote control for easy switching between devices
- RS232 interface provides you with remote/off-site control
- Front panel push-buttons
- 3.5mm audio connections

Hårdvara

| | |
|---------------|---------------------|
| Garantipolicy | 2 Years |
| AV-ingång | VGA 3,5 mm audio |
| Portar | 4 |
| AV-utgång | VGA 3,5 mm audio |
| Audio | Ja |

Prestanda

| | |
|---------------------------|----------------------------------|
| Maximal analog upplösning | 1920x1200 (PC), and 1080p (HDTV) |
| Bandbredd | 650 MHz (-3dB) max |

Kontakt(er)

| | |
|-------------|--|
| Connector A | VGA (15-stifts, High Density D-Sub) 3.5 mm minijack (3-polig) |
| Connector B | VGA (15-stifts, High Density D-Sub) 3.5 mm minijack (3-polig) |

Ström

| | |
|--------------|----------------------|
| Power Source | AC-adapter medföljer |
|--------------|----------------------|

| | |
|----------------------|--------------|
| Inspänning | 100 - 240 AC |
| Inström | 0.6A |
| Utspänning | 5 DC |
| Utström | 2.6A |
| Polaritet på mittpol | Positiv |
| Strömförbrukning | 5 |

Utseende

| | |
|--------------|-------------------|
| Färg | Svart |
| Kabinetttyp | Aluminium |
| Produktlängd | 6.5 in [16.5 cm] |
| Produktbredd | 11.3 in [28.7 cm] |
| Produkt höjd | 1.6 in [40.0 mm] |
| Produktvikt | 3.3 lb [1.5 kg] |

Förpackning

| | |
|----------------------------|-------------------|
| Package Length | 12.7 in [32.2 cm] |
| Package Width | 2.7 in [68.0 mm] |
| Package Height | 12.9 in [32.7 cm] |
| Fraktvikt (förpackning) | 4.7 lb [2.1 kg] |

Vad det är i lådan

| | |
|-----------------|---------------------------------------|
| Ingår i paketet | IR Remote Control |
| | 4x1 VGA Switch |
| | 3ft. VGA Cable |
| | Universal Power Adapter (US/UK/EU/AU) |

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

