

4 Port VGA Video Audio Switch with RS232 control

Product ID: VS410RVGAA



The VS410RVGAA 4 Port VGA Video Audio Switch with RS232 control lets you switch between four separate VGA signals, as well as the corresponding audio, for output to a single display or projector at resolutions up to 1920x1200 (PC) or 1080p (HDTV).

An ideal solution for situations where VGA and audio input ports are scarce, the VGA switch eliminates the hassle of having to swap out connections to your display and audio receiver, while letting you select the video source quickly and easily at the push of a button.

The VGA switch also features convenient remote switching capabilities through either RS232 serial remote control, or the included IR remote control - allowing you to switch between VGA input signals from a distance and in turn providing a convenient addition to presentation displays, trade shows, security environments and more.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Great for use in presentations, trade shows, conferences, retail, and entertainment applications
- Excellent solution for connecting and switching between multiple PC/HDTV's to one display
- Perfect for use in boardroom settings to let visitors connect to your display or projector

Features

- Supports resolutions up to 1920x1200 (1080p)

- Supports VGA Video bandwidth of 650 MHz
- RS232 interface provides you with remote/off-site control
- 3.5mm audio connections
- Front panel push-buttons
- Includes an easy-to-use remote control for easy switching between devices

Hardware

Warranty	2 Years
AV Input	VGA 3.5 mm Audio
Ports	4
AV Output	VGA 3.5 mm Audio
Audio	Yes

Performance

Maximum Analog Resolutions	1920x1200 (PC), and 1080p (HDTV)
Bandwidth	650 MHz (-3dB) max

Connector(s)

Connector A	VGA (15 pin, High Density D-Sub) 3.5 mm Mini-Jack (3 Position)
Connector B	VGA (15 pin, High Density D-Sub) 3.5 mm Mini-Jack (3 Position)

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.6A



Output Voltage	5 DC
Output Current	2.6A
Center Tip Polarity	Positive
Power Consumption (In Watts)	5

Physical Characteristics

Color	Black
Material	Aluminum
Product Length	6.5 in [16.5 cm]
Product Width	11.3 in [28.7 cm]
Product Height	1.6 in [40 mm]
Weight of Product	3.3 lb [1.5 kg]

Packaging Information

Package Length	12.7 in [32.2 cm]
Package Width	2.7 in [68 mm]
Package Height	12.9 in [32.7 cm]
Shipping (Package) Weight	4.7 lb [2.1 kg]

What's in the Box

Included in Package	4x1 VGA Switch
	IR Remote Control
	Universal Power Adapter (US/UK/EU/AU)
	3ft. VGA Cable

****Product appearance and specifications are subject to change without notice.***

