

4 Port DisplayPort Video Switch with Audio & IR Remote Control

Productcode: VS421DP



The VS421DP 4-port DisplayPort Switch offers superb multi-source control for demanding high-resolution display applications that require true high definition capability.

Supporting a native display resolution of 2560x1600 and 7.1 channels of audio (when connected to supporting displays and sources), this simple, yet comprehensive DisplayPort A/V Switch features both push-button and infrared remote control and offers a compact form factor design.

Application Diagram

Backed by our 2-year warranty and free lifetime technical support, the VS421DP delivers a reliable solution for switching between multiple DisplayPort audio/video sources.

Certificaties, rapporten en compatibiliteit



Toepassingen

- High resolution medical imaging and Health care display, such as MRI and Xray display.
- High resolution digital signage requiring multiple sources with one display.
- Multimedia design, multimedia post-production and video editing.

- High resolution digital images in education in the classroom, lecture halls, and conference rooms with multiple sources to one DisplayPort monitor.

Eigenschappen

- Supports resolutions up to 2560 x 1600 @ 60Hz, beyond 1080p
- 7.1 Channel High Definition Audio pass-through (with displays and sources that support DisplayPort audio)
- Supports DisplayPort ++ for use with VGA, DVI, or HDMI displays (please see accessories)
- Supports native DisplayPort computer connections - no adapter required
- DisplayPort 1.1 Compliant
- Supports DDC2B monitor detection

Hardware

Garantiebeleid	2 Years
AV-ingang	DisplayPort
Poorten	4
AV-uitgang	DisplayPort
Audio	Ja
Industriestandaarden	DDC, EDID, DisplayPort 1.1

Prestaties

Maximale kabellengte	32.8 ft [10 m]
Maximale digitale resoluties	2560x1600 @ 60Hz
Ondersteuning breedbeeld:	Ja

Connector(en)

Connector A	4 - DisplayPort (20-polig)
Connector B	1 - DisplayPort (20-polig)

Speciale
opmerkingen /
vereisten

Notitie

Source (PC) and display must both support audio pass through for audio functionality

Indicatoren

LED-indicatoren

4 - Green - Online and Display indicator (One LED per port)

Voeding

Voedingsbron

Inclusief wisselstroomadapter

Ingangsspanning

110V-240V AC

Uitgangsspanning

5 DC

Uitgangsstroom

2A

Polariteit pin midden

Positief

Stekkertype

M

Vermogensopname

10

Gebruiksomgeving

Bedrijfstemperatuur

0°C to 40°C (32°F to 104°F)

Opslagtemperatuur

-20°C to 60°C (-4°F to 140°F)

Vochtigheid

0~80% RH

Fysieke
eigenschappen

Kleur

Zwart

Type behuizing

Aluminium

Lengte product

5.2 in [13.1 cm]

Breedte product

2.6 in [6.5 cm]

Hoogte product

1.0 in [2.6 cm]

Gewicht product

17.6 oz [500 g]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	10.6 in [27 cm]
Package Width	7.3 in [18.6 cm]
Package Height	3.1 in [80 mm]
Verzendgewicht (verpakt)	1.3 lb [0.6 kg]

Wat wordt er meegeleverd

Meegeleverd	1 - 4 Port DisplayPort Switch
	1 - IR Remote Control
	1 - Universal Power Adapter (NA/UK/EU/AUS)
	1 - Manual

Garantiebepalingen

Warranty	2 Jaar
----------	--------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.