

4x4 HDMI Matrix Video Switch Splitter with Audio and RS232

Produkt ID: VS440HDMI



The VS440HDMI 4x4 HDMI® Audio/Video Matrix Switch/Splitter (with Audio and RS232) lets you share up to 4 distinct HDMI or DVI inputs (using HDMI to DVI adapters - not included), with audio, between 4 independent displays or projectors.

Providing convenient front push-button and RS232 PC software control, this matrix switch allows each input and the corresponding audio to be switched individually, meaning that different A/V sources can be shown on each output, or a single source can be output to several offering maximum flexibility.

The switcher features a front panel LCD display for easy status monitoring, plus an included remote control and IR extender module for simple control from a distance.

Designed to provide maximum functionality while saving space, the HDMI Video Matrix Switch can be used as a standalone solution or rack-mounted using ear-mounts (included).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Ideal for connecting/switching multiple sources in Test Bench Facilities, Data Centers, Help Desks and Video Broadcasting Facilities
- Perfect for digital signage applications in retail environments requiring more than one media player or PC to be connected

- Allow trainees/students to see what is on your display and then switch them back to their own display after the demonstration completes
- Run multimedia presentations with supporting data displayed on another monitor in business conference rooms or at trade shows
- Take full control of your A/V sources and displays/projectors - select any source on any display

Funktioner

- Included software allows storage of up to 4 distinct display combinations
- Allows four PCs/Media Players to provide video to four displays
- Allows storage and recall of a display combination using front panel buttons
- Supports connection to DVI displays using HDMI® to DVI adapters (sold separately)
- Equipped with easy to use front panel selection buttons
- Supports resolutions up to 1920x1200 or 1080p
- 10m (32ft) Maximum cable length
- Front panel LCD for easy status monitoring
- Includes remote control and IR extension module
- RS232 interface for PC control

Hårdvara

Garantipolicy	2 Years
Portar	4
AV-ingång	HDMI
AV-utgång	HDMI
Kablage	HDMI
Audio	Ja
Hyllmonterbar	Ja

Prestanda



Maximal kabellängd	32.8 ft [10 m]
Stödda upplösningar	1920x1200 or 1080p
Stöd för widescreen	Ja
Bandbredd	225MHz

Kontakt(er)

Kontakttyp(er)	DB-9 (9-stifts, D-Sub)
Connector A	HDMI (19-stifts)
Connector B	HDMI (19-stifts)

Ström

Power Source	AC-adapter medföljer
Inspänning	100 - 240 AC
Inström	0.6A
Utspänning	12V DC
Utström	1.5A
Polaritet på mittpol	Positiv
Kontakttyp	M
Strömförbrukning	18

Miljö

Drifttemperatur	0°C to 70°C (32°F to 158°F)
Förvaringstemperatur	-20°C to 85°C (-4°F to 185°F)
Luftfuktighet	0~95%

Utseende

Färg	Svart
Kabinetttyp	Stål
Produktlängd	17.3 in [44.0 cm]



Produktbredd	7.3 in [18.5 cm]
Produkt höjd	1.7 in [42.0 mm]
Produktvikt	5.2 lb [2.4 kg]

Förpackning

Package Length	22.9 in [58.1 cm]
Package Width	10.4 in [26.3 cm]
Package Height	3.5 in [90.0 mm]
Fraktvikt (förpackning)	6.9 lb [3.1 kg]

Vad det är i lådan

Ingår i paketet	HDMI Matrix Selector Switch
	6 ft [1.83 m] RS232 Cable
	IR Remote Control
	IR Extender
	AAA-batterier
	Rack Mount Brackets
	Screws for rack mount brackets
	Universal Power Adapter (US/UK/EU/AU)
	Software Installation CD
	Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

