

Flera videoingångar med ljud till HDMI-switch - HDMI/VGA/Komponent

Produkt ID: VS721MULTI



The VS721MULTI Multiple Video Input to HDMI® Switcher enables users to switch between 7 different audio-video sources to a single HDMI-equipped display.

This versatile switcher is the perfect solution for combining digital and analog video sources (RGB/YPbPr/YCbCr) with your digital HDMI® display, eliminating the cost of upgrading individual components (i.e. DVD player, PC, VCR, etc.).

An all-in-one multimedia solution, the video converter/switcher includes support for full high definition 1080p video resolution as well as digital and analog audio. Plus, the switch features RS232 remote serial control, and includes a convenient IR remote control for switching between video sources .

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Convert analog and digital video to HDMI® for a variety of applications such as switching between consumer electronics devices (e.g. Blu-ray Disc™ players, satellite receivers, video game consoles and other devices)

Funktioner

- Supports analog PC Resolution input and output up to WUXGA (1920x1200) @ 60Hz

- HDMI® and HDCP compliant
- Supports analog HDTV RGB/YPbPr/YCbCr input, output up to 1080p @ 60Hz

Hårdvara

Garantipolicy	2 Years
AV-ingång	HDMI
	S-Video
	Composite
	VGA
	Component
Portar	7
AV-utgång	HDMI
Kablage	HDMI
Audio	Ja
Industristandarder	High Speed HDMI®, HDCP

Prestanda

Maximal analog upplösning	VGA: 1920x1200, YPbPr: 1920x1080
Maximal digital upplösning	1920x1200
Stödda upplösningar	Support VGA mode, 640x480, 720x400, 800x600, 848x480, 1024x768, 1152x864, 1280x720, 1280x768, 1280x800, 1280x960, 1280x1024, 1360x768, 1400x1050, 1440x900, 1440x1050, 1600x1200, 1680x1050, 1920x1080, 1920x1200
	Support YPbPR mode, 720x480, 720x576, 720x480, 720x576, 1280x720, 1920x1080, 1920x1080
Stöd för widescreen	Ja

Kontakt(er)



Connector A	HDMI (19-stifts)
	VGA (15-stifts, High Density D-Sub)
	Komponentvideo (3 x RCA)
	S-Video (4-stifts, Mini-DIN)
	Kompositvideo (1 x RCA)
	RCA
	3.5 mm minijack (3-polig)
Connector B	HDMI (19-stifts)

Mjukvara

OS-kompatibilitet	Windows® 10 (32/64), 8/8.1 (32/64), 7 (32/64), Vista(32/64), XP(32/64), 2000 Windows® Server 2008 R2, 2003(32/64)
-------------------	--

Indikatorer

LED-indikatorer	1 - HDMI
	2 - HDMI
	3 - HDMI
	4 - VGA
	5 - YPbPr
	6 - CVSB
	7 - S-VIDEO

Ström

Power Source	AC-adapter medföljer
Inspänning	100 - 240 AC
Inström	0.6 A
Utspänning	12V DC



Utström	1.5 A
Polaritet på mittpol	Positiv
Kontakttyp	M
Strömförbrukning	18

Miljö

Drifttemperatur	0°C to 70°C (32°F to 158°F)
Förvaringstemperatur	-20°C to 85°C (-4°F to 185°F)
Luftfuktighet	0% to 95% RH Non-Condensing

Utseende

Färg	Svart
Kabinetttyp	Aluminium
Produktlängd	15.1 in [38.4 cm]
Produktbredd	6.8 in [17.3 cm]
Produkt höjd	1.8 in [45.0 mm]
Produktvikt	4.0 lb [1.8 kg]

Förpackning

Package Length	18.1 in [45.9 cm]
Package Width	10.2 in [26.0 cm]
Package Height	3.5 in [90.0 mm]
Fraktvikt (förpackning)	6.0 lb [2.7 kg]

Vad det är i lådan

Ingår i paketet	multiple format to HDMI audio video switch
	IR remote control
	mounting kit
	RS232 serial cable (6 ft.)



RS-232 control software CD

universal power adapter (NA, EU, UK, AU)

instruction manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

