

Wall Mount Workstation, Full Motion Sit Stand Desk w/ Height Adjustable VESA Monitor Arm & Keyboard Tray, Ergonomic Wall Mounted Computer Workstation, Single 27"/34" Display - TAA

Produkt-ID: WALL-WORKSTATION-S



This Sit-Stand Wall Mount Workstation allows you to create an ergonomic standing desk setup. This is the ideal solution for installations with limited space for a traditional desk, such as offices, labs, clinics, or warehouses. The workstation features a foldable keyboard with an ambidextrous slide-out mousepad tray. The spring-assisted arm allows for height adjustment and lets you alternate between sitting and standing without interrupting your workflow. Adjust your workstation up, down, left or right, to suit the user's ergonomic requirements.

Modify your position with one smooth motion using the built-in handle. Hold and lift the work surface with a range of up to 17.2in (43.8cm) to adjust the workstation's height. You can change the height adjustment tension to suit the user's needs. The VESA (75x75/100x100) monitor mount features an independent height adjustment with a range of up to 4.8in (12.4cm) along the monitor column.

The VESA monitor mount supports one monitor (up to 27" or 34" ultrawide), tilts +35°/ -5°, and rotates up to 360° to accommodate vertical and horizontal monitor orientations.

The workstation can reach up to 37.6in (95.6cm) from the wall when the keyboard tray is extended.

The workstation features a large keyboard tray (17.6x8.1in / 44.9x20.7cm). A retractable mousepad tray (8.6x8.4in / 21.9x21.3cm) slides-out to the left or right to suit the user's needs.

To make the most of the workspace, tuck the workstation away with a slim 13.1in (33.3cm) profile from the wall and free up space when not in use. The articulating arm swivels +/-90°, and the keyboard tray folds up to 90°. Built-in mouse and handheld scanner holders and cable management solution complement the design.

Combine with CPUWALLMNT to wall mount a computer nearby for a complete workstation solution.

The wall-mounted computer workstation is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **WALL MOUNT WORKSTATION:** Ergonomic sit-stand desk with spring-assisted articulating arm, keyboard tray and retractable mouse tray - VESA compatible mount (75x75 / 100x100) - Monitor capacity up to 17.6lb (8kg) and 27" (or 34" ultrawide)
- **FOLDABLE WORKSTATION:** Tilt 90° and stow away when not in use (13.1"/33.3cm from wall); Adhesive strip secures keyboard - Slide-out left/right mouse tray - Extended arm allows monitor to reach 21.5in (54.8cm) & keyboard tray 37.6in (95.6cm) from wall
- **WIDE RANGE OF MOTION:** Height-adjustable wall-mounted workstation swivels +/-90°, arm bends +65/-30° (up/down) - Single monitor mount supports +35/-5° tilt, 360° rotation - One-touch height adjustment of the monitor up to 4.9in (12.4cm)
- **WALL MOUNT STANDING DESK:** Adjust your workstation in a single motion using the built-in handle - PC workstation height adjustment range of up to 17.2in (43.6cm) - Add CPUWALLMNT (sold separately) to wall-mount a computer nearby - Adjustment tools included
- **INTUITIVE DESIGN:** Removable mouse tray & wrist rest cover allow for frequent cleaning of all high-touch surfaces, ideal for a shared workstation in an office, clinic, or warehouse - Built-in cable management - Mouse and handheld scanner holders

Hardware

Garantiebestimmungen 2 Years

Wandmontierbar Ja

Kabelmanagement Ja

Inklusive Werkzeuge Ja

Gelenk Ja

Anzahl der unterstützten Displays	1
Montageoptionen	Wandmontage
Minimum Profile from Wall	13.1 in [333 mm]
VESA-Lochmuster	75x75 mm 100x100 mm

Leistung

Gewichtskapazität	17.6 lb [8 kg]
Weight Capacity of Keyboard Tray	5.5 lb [2.5 kg]
Maximale Bildschirmgröße	27" 34" (21:9)
Geeignet für Curved Display	Nein
Fits UltraWide Displays	Ja
Höhenverstellung	Ja
Maximale Höhe	36.5 in [926 mm]
Minimum Arm Extension	14.5 in [369 mm]
Maximale Armlänge	21.6 in [548 mm]
Neigung	+35° / -5°
Keyboard Tray Tilt	0 to 90°
Schwenkung/Drehung	+90° / -90°
Displayrotation	360°
Diebstahlsicherung	Nein

Spezielle
Hinweise/Anforder

ungen

Hinweis

When using ultrawide (21:9) monitors only landscape position is supported.

Physische Eigenschaften

Farbe	Silber
Gehäusety	Aluminium und Stahl
Keyboard Tray Width	17.7 in [449 mm]
Keyboard Tray Depth	8.1 in [207 mm]
Produktlänge	37.6 in [95.6 cm]
Produktbreite	26.3 in [66.8 cm]
Produkthöhe	36.5 in [92.6 cm]
Produktgewicht	19.3 lb [8.8 kg]

Verpackungsinformationen

Paketmenge	1
Paketlänge	16.6 in [42.2 cm]
Paketbreite	22.9 in [58.2 cm]
Pakethöhe	8.8 in [22.4 cm]
Versandgewicht (Verpackung)	23.4 lb [10.6 kg]

Verpackungsinhalt

Im Paket enthalten	1 - Monitorarm
	1 - Tastaturablage
	1 - Säule
	1 - VESA-Monitorbefestigung
	1 - Wandhalterung
	2 - Adhesive Strips

- 4 - Montageschrauben
- 4 - Betonanker
- 1 - 6mm Inbusschlüssel
- 1 - 5mm Inbusschlüssel
- 1 - 2.5mm Hex Hey
- 1 - M6x8mm Screw
- 4 - Schrauben, M4 x 10 mm
- 4 - Schrauben M6x12 mm
- 3 - M6x10mm Screws
- 1 - M8x30mm Screw
- 2 - M3x8mm Screws
- 1 - Steckschlüssel
- 1 - Metall-Unterlegscheibe
- 1 - Kunststoff-Unterlegscheibe
- 1 - Benutzerhandbuch

Garantieinformationen

Warranty

2 Jahre

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.