

12U Wall-Mount Bracket for Shallow Rack-Mount Equipment - 13.75in. (34.93cm) Deep

Product ID: WALLMNT12



This wall-mount bracket provides 12U of space for mounting shallow rack-mount equipment that's 13.75 in. (34.93 cm) deep or less to the wall, such as patch panels or network switches.

The 12U rack optimizes your working space by efficiently mounting your shallow equipment on your wall instead of taking up desk space or other usable surface areas. It's the perfect solution for your space-limited SoHo (small office, home office) environment or server room because it doesn't take up any floor space.

The wall rack is constructed of solid steel to ensure a sturdy and safe mounting solution for your mission-critical equipment. Also, because the wall-mount rack's mounting holes are positioned 16 in. apart, it exactly matches standard drywall construction framework to ensure simple and secure wall-stud anchoring. The rack also features a rear access panel that can be used to easily run cabling into the rack.

Cage nuts and screws are included with the wall-mount bracket, to save you the hassle of sourcing separate mounting hardware.

If you're looking for a shallow mounting solution with fewer rack units, StarTech.com also offers a 6U wall-mount bracket, and an 8U wall-mount bracket.

The WALLMNT12 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Mount equipment that is up to 12 inches deep on your wall
- Organize cabling or equipment in your network closet, wiring closet, back office or IDF

- Save space in your SoHo (small office, home office) or server room, by mounting equipment to the wall instead of taking up floor space

Features

- Improve efficiency in your office or server room by mounting shallow equipment to the wall
- Sturdy installation of mission critical equipment with solid steel design
- Hassle-free setup with wall mounting holes spaced 16 in. apart, matching standard dry-wall framework
- Cage nuts and screws included
- Rear access panel for cable management
- 12U wall-mount design

Prominence

Warranty	Lifetime
Description CDW 75 - 1st Line	StarTech.com 12U 13.75" Wall Mount Patch Panel Bracket - Shallow Equipment

Hardware

Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	12U
Special Features	Ships Fully Assembled Wall-Mountable
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	125.3 lb [56.7 kg]
-----------------	--------------------

Physical Characteristics

Color	Black
-------	-------



Construction Material Steel

Product Measurements

Product Length	13.8 in [34.9 cm]
Product Width	19.6 in [49.9 cm]
Product Height	21.3 in [54.1 cm]
Weight of Product	19.2 lb [8.7 kg]
Maximum Mounting Depth	13.8 in [34.9 cm]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	20.9 in [53.0 cm]
Package Width	15.1 in [38.3 cm]
Package Height	22.3 in [56.7 cm]
Shipping (Package) Weight	24.2 lb [11.0 kg]

What's in the Box

Included in Package	Wall-Mount Bracket
	M5 Cage Nuts
	M5 Screws
	M6 K-Nut
	Wood Screws
	User Manual

**Product appearance and specifications are subject to change without notice.*

