

6U Wall-Mounting Bracket for Patch Panel - 13.75 in. Deep

Product ID: WALLMOUNT6



The WALLMOUNT6 6U 13.75 in. Deep Wall Mounting Bracket for Patch Panel delivers a sturdy and dependable equipment storage option, allowing you to wallmount equipment for a more efficient and accessible operating environment.

The mounting bracket features an all-steel design and is suitable for mounting patch panels, or other slim 19in equipment to a wall.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Wall mount patch panels and other slim 19" rackmount equipment

Features

- Sturdy cold rolled steel construction
- 6U rack height
- 20 kg (44 lbs) weight capacity

Hardware	Warranty	Lifetime
	Wallmountable	Yes

Rack Type	2-Post
Frame Type	Open Frame
U Height	6U
Special Features	U-Markings
Special Features	Wall-Mountable
Special Features	Ships Fully Assembled
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance	Weight Capacity	44.2 lb [20 kg]
--------------------	-----------------	-----------------

Physical Characteristics	Color	Black
	Construction Material	Steel

Product Measurements	Product Length	13.8 in [3.5 cm]
	Product Width	19.6 in [5.0 cm]
	Product Height	10.7 in [2.7 cm]
	Weight of Product	6.4 lb [2.9 kg]
	Maximum Mounting Depth	13.6 in [3.5 cm]

Packaging Information	Flat Pack (Assembly Required)	No
	Package Length	20.6 in [5.2 cm]
	Package Width	15.0 in [3.8 cm]
	Package Height	11.8 in [3.0 cm]
	Shipping (Package) Weight	4.4 lb [2.0 kg]

What's in the Box	Included in Package	6U Wall Mount Rack
	Included in Package	Instruction Manual
	Included in Package	M6 Screws
	Included in Package	M6 Cage Nuts

****Product appearance and specifications are subject to change without notice.***

