

6U Wall Mount Network Rack- 14 Inch Deep(Low Profile)- 19" Patch Panel Bracket for Shallow Server and IT Equipment, Network Switches- 44lbs/20kg Weight Capacity, Black

**Product ID:** WALLMOUNT6



The WALLMOUNT6 6U 13.78 in. Deep Wall Mounting Bracket for Patch Panel delivers a sturdy and dependable equipment storage option, allowing you to wallmount equipment for a more efficient and accessible operating environment.

The mounting bracket features an all-steel design and is suitable for mounting patch panels, or other slim 19in equipment to a wall.

Backed by a StarTech.com Lifetime warranty.

## Certifications, Reports and Compatibility



## Applications

- Wall mount patch panels and other slim 19" rackmount equipment

## Features

- **6U WALL MOUNT RACK:** This 6U 35cm deep wall mounting bracket has an open frame, 2 post design with a maximum mounting depth of 35 cm [13.78 in.] and a maximum weight capacity of 19.9kg [44.2lb]
- **EASY TO INSTALL:** The 6U wall mounting bracket ships fully assembled and comes complete with M6 Screws and

M6 Cage Nuts for easier installation, to save you the hassle of sourcing separate mounting hardware

- **COLD-ROLLED STEEL CONSTRUCTION:** Made of sturdy cold rolled steel, you can rely on this mounting bracket to keep your network equipment safe and sound. This bracket is perfect in areas where space is at a premium
- **OPTIMIZE STORAGE SPACE:** The 6U wall mounting bracket delivers a dependable equipment storage option, allowing you to wall mount equipment for a more efficient and accessible operating environment
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this wallmount bracket is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

#### Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	6U
Special Features	Ships Fully Assembled
	U-Markings
	Wall-Mountable
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

#### Performance

Weight Capacity	44.1 lb [20 kg]
-----------------	-----------------

---

#### Physical Characteristics

Color	Black
Construction Material	Steel
Material	Steel
Product Length	13.8 in [35.0 cm]
Product Width	19.6 in [49.8 cm]

Product Height	10.7 in [27.3 cm]
Weight of Product	9.9 lb [4.5 kg]
Maximum Mounting Depth	13.8 in [35 cm]

---

**Packaging Information**

Flat Pack (Assembly Required)	No
Package Quantity	1
Package Length	20.7 in [52.6 cm]
Package Width	15.3 in [38.8 cm]
Package Height	12.2 in [31.0 cm]
Shipping (Package) Weight	13.3 lb [6.0 kg]

---

**What's in the Box**

Included in Package	1 - 6U Wall Mount Rack
	12 - M6 Screws
	12 - M6 Cage Nuts
	12 - Plastic Washers
	4 - M5-25 Flat-head screws
	4 - Plastic Wall Anchors
	1 - Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***