

2U 19in Hinged Wall Mount Bracket for Patch Panels

Product ID: WALLMOUNTH2



The WALLMOUNTH2 2U 19in Hinged Wall Mounting Bracket for Patch Panels is 6in deep and sturdily designed to provide a dependable solution for mounting a patch panel, or other slim 19in networking equipment to a wall.

The patch panel wall mount features a hinged design for easy access to configuration buttons, ports and cables. The wall mounting holes are spaced 16 in. apart, making it suitable for mounting on almost any wall, based on common wall-frame stud spacing.

Backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility

Applications

- Wall mount patch panels and other slim 19" rackmount equipment

Features

- Sturdy cold rolled steel construction
- 2U rack height
- Hinged side panel for easy equipment access
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs
- 10 kg (22 lbs) weight capacity

Hardware

Warranty	2 Years
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	2U
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	22.1 lb [10 kg]
-----------------	-----------------

Physical Characteristics

Color	Black
Construction Material	Steel

Product Measurements

Product Length	5.9 in [15.1 cm]
Product Width	19.7 in [50.1 cm]
Product Height	3.5 in [88.0 mm]
Weight of Product	2.6 lb [1.2 kg]
Maximum Mounting Depth	5.8 in [14.8 cm]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	20.2 in [51.4 cm]
Package Width	7.0 in [17.8 cm]



Package Height	4.0 in [10.1 cm]
Shipping (Package) Weight	35.3 oz [1000.0 g]

What's in the Box

Included in Package	Wall-Mount Rack
	M6 Screws
	M6 Cage Nuts
	Plastic Washers
	Wall Screws
	Plastic Anchors

****Product appearance and specifications are subject to change without notice.***

