

WiFi to HDMI Video Wireless Extender with Audio - High-Definition

Produkt ID: WIFI2HD2



The WIFI2HD2 HDMI® over Wi-Fi Adapter enables you to send an HDMI audio/video signal from a laptop or desktop computer, to a remote projector or display over a wireless IP network.

Unlike other wireless video solutions which require devices at both ends of the connection, the WIFI2HD2 is a single compact device that can be situated by your remote display / projector, making it perfect for business applications such as boardroom presentations. The only requirement is the included software must be installed on a computer to connect to the WIFI2HD2.

Compatible with Wireless-N (IEEE 802.11n) and backward compatible with Wireless-G (802.11 g) networks, this HDMI over WiFi extender supports resolutions up to 1080p for optimum video and audio quality. The extender also features an integrated USB port, for keyboard/mouse connection.

The WIFI2HD2 HDMI Wi-Fi Adapter is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Display spreadsheets, and graphs wirelessly on a display or projector
- Deliver multimedia presentations to HDMI displays at trade-shows and vendor fairs without running cables

Funktioner

- Supports resolutions up to 1080p
- Optional RJ-45 Ethernet port for LAN connectivity
- Integrated USB port for mouse/keyboard connection
- Compliant with IEEE 802.11n/g wireless adapters
- Wireless transmission up to 180 ft (55m) on open sites

Hårdvara

Garantipolicy	2 Years
Portar	1
AV-utgång	HDMI
Kablage	Trådlöst Ethernet
Audio	Ja
Industristandarder	IEEE 802.11n Draft 3.0, IEEE 802.11g
Kedjekoppling	Nej

Prestanda

Stödda upplösningar	Standard: 1600x1200, 1280x1024, 1280x768, 1024x768, 800x600 Widescreen: 1920x1080, 1680x1050, 1440x900, 1366x768, 1280x800, 1280x720
Frekvensområde	5 GHz ISM Bands (5.15-5.85 GHz) 2.4 GHz ISM Bands (2.412~2.484 GHz)
Allmänna specifikationer	Note: 1080p video resolution is supported only on Intel® HD Family Graphics Adapters (HD 2000 or above). All other graphics adapters will be limited to 720p.

Kontakt(er)

Connector A	RJ-45 Trådlös G (IEEE 802.11g)
-------------	---------------------------------------



		Trådlös N (IEEE 802.11n)
	Connector B	HDMI (19-stifts)
		USB Type-A (4-stifts) USB 2.0
		3.5 mm minijack (3-polig)
<hr/>		
Mjukvara	OS-kompatibilitet	Windows® 8 (32/64)/ 7 (32x64-bit)/ Vista (32/64)/ XP (32/64)NOTE: The PC2TV software is not compatible with Windows® 8.1
<hr/>		
Särskilda anmärkningar/krav	Obs.	The PC2TV software is not compatible with Windows® 8.1
<hr/>		
Indikatorer	LED-indikatorer	Power
<hr/>		
Ström	Power Source	AC-adapter medföljer
	Inspänning	100 - 240 AC
	Inström	0.2A
	Utspänning	5 DC
	Utström	1A
	Polaritet på mittpol	Positiv
	Kontakttyp	M
	Strömförbrukning	5
<hr/>		
Utseende	Färg	Svart
	Kabinetttyp	Av plast
	Kabellängd	5.1 in [13 cm]

Produktlängd	2.8 in [72 mm]
Produktbredd	2.2 in [55 mm]
Produkt höjd	1.1 in [27 mm]
Produktvikt	4.9 oz [140 g]

Förpackning

Package Length	9.0 in [22.9 cm]
Package Width	6.0 in [15.3 cm]
Package Height	3.6 in [91 mm]
Fraktvikt (förpackning)	14.1 oz [400 g]

Vad det är i lådan

Ingår i paketet	WiFi to HDMI Converter
	Universal Power Adapter (NA/UK/EU)
	Installation CD
	Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

