

Wireless Display Adapter with HDMI - 1080p

**Product ID:** WIFI2HDMC



Wirelessly broadcast your smartphone, tablet, or laptop onto any HDMI display with this wireless Miracast adapter. The HDMI over wireless adapter natively supports Miracast enabled mobile devices such as Android smartphones & tablets, and Windows 8.1 laptops, Ultrabooks & Surface tablets. Additional Software is also included with the Miracast receiver for guaranteed compatibility with Windows based computers through a standard Wi-Fi or wired LAN connection.

Keep your boardroom free of clutter by wirelessly connecting your HDMI projector to almost any mobile device. With native support for a broad range of Miracast smartphones and tablets including Samsung devices that run All-share and Screen Mirror software, this Miracast receiver is perfect for BYOD (Bring Your Own Device) office and boardroom applications.

Synergize with your co-workers by effortlessly and wirelessly sharing and switching your display between different video source devices. The Miracast adapter has an intuitive interface that ensures hassle-free operation.

Your mobile device is designed to be portable. This means the screen is too small to share with more than two people. Present big ideas on the big screen from the comfort and portability of your own smartphone, tablet, or laptop.

The WIFI2HDMC is backed by a 2-year warranty and free lifetime technical support.

## **Certifications, Reports and Compatibility**

### **Applications**

- Display audio/video content such as a presentation from your smartphone or tablet on a boardroom projector
- Share photos or video with audio from your smartphone or tablet to your home theatre system

- Display multimedia presentations on HDMI displays at trade-shows and vendor fairs from a portable smartphone or tablet

## Features

- Native compatibility with hundreds of devices (Miracast)
- Software included for additional device compatibility (Windows)
- Built-in media server for wireless or USB storage devices
- HDMI output with 1080p support
- Optional LAN port for wired devices
- Optional analog audio/video out with included cable

---

### Hardware

Warranty	2 Years
Ports	1
AV Input	HDMI
AV Output	HDMI
Cabling	Wireless Ethernet
Audio	Yes
Daisy-Chain	No

---

### Performance

Maximum Digital Resolutions	1920x1080/1080p
Wide Screen Supported	Yes
General Specifications	Supported File Formats in Media Server Mode: AVI, MPEG-1, MPEG-2, MPEG-TS, MPEG-4, 3GP, 3GP2, MOV, WMV and DVR-MS

---

### Connector(s)

Connector A	Wireless N (IEEE 802.11n)
Connector B	USB Type-A (4 pin) USB 2.0
	HDMI (19 pin)



RJ-45

3.5 mm Mini-Jack (3 Position)

---

**Software**

OS Compatibility	Windows 10 (32/64) Windows 8 / 8.1 (32/64) Windows 7(32/64) Windows Vista (32/64) Android (v.4.3 and above)
------------------	---

---

**Indicators**

LED Indicators	Power/Activity LED
----------------	--------------------

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Output Voltage	5 DC
Output Current	1A
Power Consumption (In Watts)	5

---

**Environmental**

Operating Temperature	0C to 45C (32F to 131F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	20%~80%

---

**Physical Characteristics**

Color	Black
Material	Plastic
Product Length	2.6 in [65.0 mm]
Product Width	3.3 in [85.0 mm]
Product Height	1.0 in [26.0 mm]
Weight of Product	2.8 oz [79.0 g]



---

**Packaging Information**

Package Length	6.0 in [15.2 cm]
Package Width	8.5 in [21.6 cm]
Package Height	2.1 in [54.0 mm]
Shipping (Package) Weight	14.0 oz [396.0 g]

---

**What's in the Box**

Included in Package	Wireless Display Adapter
	Power Adapter (NA)
	USB Cable to Power Adapter Port (optional for USB Power source)
	4 position A/V cable
	Quick Installation Guide

---

***\*Product appearance and specifications are subject to change without notice.***

