

WiFi to VGA Wireless Video Extender with Audio – 1280x1024 / 720p

**Product ID:** WIFI2VGA



The WIFI2VGA VGA over Wi-Fi Adapter enables you to send a VGA signal (resolutions up to 1280x1024/720p), as well as the supporting audio from a laptop or desktop computer, to a remote projector or display over a wireless IP network.

Unlike other wireless VGA solutions which require devices at both ends of the connection, the WIFI2VGA is a single compact device that can be situated by your remote display, saving the hassle of carrying a secondary device, making it perfect for business applications such as boardroom presentations and data sharing. All that is required is installation of the included software on each computer you intend to connect to the WIFI2VGA.

Compatible with Wireless N (IEEE 802.11n) and backward compatible with Wireless-G (802.11 g) networks, this wireless VGA extender supports data rates up to 150 Mbps, for optimum video and audio quality. The extender also features an integrated USB port, for keyboard/mouse connection.

The WIFI2VGA VGA Wi-Fi Adapter is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## Applications

- Send a VGA signal from your laptop to a ceiling-mounted projector in boardrooms and office buildings
- Deliver multimedia presentations to VGA displays at trade-shows and vendor fairs without running cables
- Display spreadsheets, graphs and business proposals wirelessly on a display or projector

## Features

- Wireless VGA connectivity from computer to projector or display
- Wireless transmission up to 180 ft (55m) on open sites
- Supports resolutions up to 1280x1024 / 720p
- 192kHz, 24-bit stereo audio supported
- Compliant with IEEE 802.11n/g wireless adapters
- Integrated USB port for mouse/keyboard connection
- Also offers RJ-45 Ethernet port for LAN connectivity

---

#### Hardware

Warranty	2 Years
Ports	1
Cabling	Wireless Ethernet
Audio	Yes
Industry Standards	IEEE 802.11n Draft 3.0 64/128-bit WEP, WPA, and WPA2
Daisy-Chain	No

---

#### Performance

Maximum Data Transfer Rate	150 Mbps
Maximum Analog Resolutions	Wide Screen: 720p Standard: 1280x1024
Supported Resolutions	Standard: 1280x1024, 1280x768, 1024x768, 800x600  Widescreen: 1280x720
Audio Specifications	192kHz, 24-bit stereo audio supported
Frequency Range	2.4 GHz ISM Bands (2.412-2.484 GHz)
General Specifications	DDC pass through is not supported



---

**Connector(s)**

Remote Unit Connectors	3.5 mm Mini-Jack (3 Position)
	RJ-45
	USB Type-A (4 pin) USB 2.0
	VGA (15 pin, High Density D-Sub)

---

**Software**

OS Compatibility	Windows 8(32/64bit)/ 7(32/64bit)/ Vista(32/64)/ XP(32/64)NOTE: The PC2TV software is not compatible with Windows 8.1
------------------	----------------------------------------------------------------------------------------------------------------------

---

**Special Notes / Requirements**

System and Cable Requirements	Intel P4 3.0 GHz or better 1 GB RAM 802.11 b/g/n Wi-fi or 10/100 Mbps Ethernet port
Note	The PC2TV software is not compatible with Windows 8.1

---

**Power**

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Input Current	0.2A
Output Voltage	5 DC
Output Current	1A
Center Tip Polarity	Positive
Plug Type	M

---

**Physical Characteristics**

Color	Black
Material	Plastic
Product Length	5.2 in [13.3 cm]
Product Width	2.8 in [71 mm]



Product Height	1.1 in [27 mm]
Weight of Product	4.9 oz [140 g]

---

**Packaging Information**

Package Length	9.0 in [22.9 cm]
Package Width	9.0 in [22.9 cm]
Package Height	2.5 in [63 mm]
Shipping (Package) Weight	14.1 oz [400 g]

---

**What's in the Box**

Included in Package	Wifi to VGA Adapter
	Universal Power Adapter (US/UK/EU/AUS/JP)
	Software/Driver CD
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

