

Bulk Cat 5e Ethernet Cable - 1000 ft. (304,8m) - Solid - CMR-Rated - Black - TAA Compliant

Produkt ID: WIR5ECMRBK



The WIR5ECMRBK 1000 ft Cat5e Riser Bulk Cable meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable black PVC jacket that enables you to color code your network cable drops as needed for a more organized installation. Bulk packaging is perfect for custom length runs and allows you to cover the exact distance required for your installations.

Constructed of only top quality materials, the WIR5ECMRBK delivers reliable performance and is backed by our Lifetime Warranty.

This Category 5e cable has been tested for CMR riser installations, and is ideal for in-wall, between floor and elevator shaft cable runs where CMR fire rating is required.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

Certifikat, rapporter och kompatibilitet



Användning

- Can be used in riser installations (in-wall, between floor, elevator shaft, etc.)
- Designed for use with Fast Ethernet networks

Funktioner

- CAT5e ETHERNET CABLE: 1000 ft. (304,8m) Solid 4 Pair UTP Cat5e cable is optimized for enterprise 1000 Mbps networks; 350 MHz frequency range enhances throughput capacity; Supports Power over Ethernet (PoE)
- QUALITY CONSTRUCTION: High-quality copper conductors enable a precise fit to minimize wear and signal loss; 24 AWG solid copper supporting a diverse range of Ethernet applications
- SAFETY AND RELIABILITY: Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits; Reliable Ethernet connections in applications requiring CMR rated Cat5e Cable
- APPLICATIONS: Ideal for riser installations (in-wall, between floor, elevator shafts, etc.) where CMR fire rating is required.; Can be used for network installation at home, office or educational institution
- SPECIFICATIONS: CAT5e; Black; 1000 foot (304,8 meter); 10/100/1000Mbps; 350 MHz; PoE; UTP; 24AWG Pure Bare Copper; CMR Rated (Riser); TAA

Hårdvara

Garantipolicy	Lifetime
Antal ledare	4 Pair UTP
Kabelmanteltyp	PVC - Polyvinyl Chloride
Brandteknisk klass	CMR-klass (Riser)

Prestanda

Kabelklassificering	CAT5e - 350 MHz
---------------------	-----------------

Utseende

Färg	Svart
Tråddimension	24 AWG

Ledningstyp	Solid koppar
Kabellängd	1000.0 ft [304.9 m]
Produktlängd	1000.0 ft [304.9 m]
Produktbredd	0.0 in [0.0 cm]
Produkthöjd	0.0 in [0.0 cm]
Produktvikt	19.7 lb [9.0 kg]

Förpackning

Förpackningsantal	1
Paketets längd	8.9 in [22.7 cm]
Paketets bredd	14.3 in [36.3 cm]
Paketets höjd	14.4 in [36.6 cm]
Fraktvikt (förpackning)	21.5 lb [9.8 kg]

Vad det är i lådan

Ingår i paketet	1 - 1000 ft Bulk Roll of Black CMR Cat5e Solid UTP Cable
-----------------	--

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.