

Bulk Cat 5e Ethernet Cable - 1000 ft. - Solid - CMR-Rated - White

Produkt ID: WIR5ECMRWH



The WIR5ECMRWH 1000 ft Cat5e Riser Bulk Cable meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable white PVC jacket that enables you to color code your network cable drops as needed for a more organized installation. Bulk packaging is perfect for custom length runs and allows you to cover the exact distance required for your installations.

Constructed of only top quality materials, the WIR5ECMRWH delivers reliable performance and is backed by our Lifetime Warranty.

This Category 5e cable has been tested for CMR riser installations, and is ideal for in-wall, between floor and elevator shaft cable runs where CMR fire rating is required.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

Certifikat, rapporter och kompatibilitet

Användning

- Can be used in riser installations (in-wall, between floor, elevator shaft, etc.)
- Designed for use with Fast Ethernet networks

Funktioner

- UL Listed CMR Riser Fire Rating
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Constructed with top quality components
- High quality 24 WG copper wire
- Foot-marked cable

Hårdvara

Garantipolicy	Lifetime
Antal ledare	4 Pair UTP
Kabelmanteltyp	PVC - Polyvinyl Chloride
Brandteknisk klass	CMR-klass (Riser)

Prestanda

Kabelklassificering	CAT5e - 350 MHz
---------------------	-----------------

Utseende

Färg	Vit
Tråddimension	24 AWG
Ledningstyp	Solid koppar
Kabellängd	1000.0 ft [304.9 m]
Produktlängd	1000.0 ft [304.9 m]
Produktbredd	0.2 in [5.0 mm]
Produkthöjd	0.2 in [5.0 mm]
Produktvikt	19.8 lb [9.0 kg]



Förpackning

Förpackningsantal	1
Package Length	13.9 in [35.3 cm]
Package Width	13.9 in [35.2 cm]
Package Height	8.9 in [22.7 cm]
Fraktvikt (förpackning)	21.9 lb [9.9 kg]

Vad det är i lådan

Ingår i paketet	1000 ft Bulk Roll of White CMR Cat5e Solid UTP Cable
-----------------	--

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

