

Bulk Cat 5e Ethernet Cable - 1000 ft. - Solid - CMR-Rated - White

Product ID: WIR5ECMRWH



The WIR5ECMRWH 1000 ft Cat5e Riser Bulk Cable meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable white PVC jacket that enables you to color code your network cable drops as needed for a more organized installation. Bulk packaging is perfect for custom length runs and allows you to cover the exact distance required for your installations.

Constructed of only top quality materials, the WIR5ECMRWH delivers reliable performance and is backed by our Lifetime Warranty.

This Category 5e cable has been tested for CMR riser installations, and is ideal for in-wall, between floor and elevator shaft cable runs where CMR fire rating is required.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

Certifications, Reports and Compatibility

Applications

- Can be used in riser installations (in-wall, between floor, elevator shaft, etc.)
- Designed for use with Fast Ethernet networks

Features

- UL Listed CMR Riser Fire Rating
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Constructed with top quality components
- High quality 24 WG copper wire
- Foot-marked cable

Hardware

| | |
|-----------------------|--------------------------|
| Warranty | Lifetime |
| Number of Conductors | 4 Pair UTP |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Fire Rating | CMR Rated (Riser) |

Performance

| | |
|--------------|-----------------|
| Cable Rating | CAT5e - 350 MHz |
|--------------|-----------------|

Physical Characteristics

| | |
|-------------------|---------------------|
| Color | White |
| Wire Gauge | 24 AWG |
| Conductor Type | Solid Copper |
| Cable Length | 1000.0 ft [304.9 m] |
| Product Length | 1000.0 ft [304.9 m] |
| Product Width | 0.2 in [5 mm] |
| Product Height | 0.2 in [5 mm] |
| Weight of Product | 19.8 lb [9.0 kg] |

Packaging Information

| | |
|------------------|-------------------|
| Package Quantity | 1 |
| Package Length | 13.9 in [35.3 cm] |



| | |
|---------------------------|-------------------|
| Package Width | 13.9 in [35.2 cm] |
| Package Height | 8.9 in [22.7 cm] |
| Shipping (Package) Weight | 21.9 lb [9.9 kg] |

What's in the Box

| | |
|---------------------|--|
| Included in Package | 1000 ft Bulk Roll of White CMR Cat5e Solid UTP Cable |
|---------------------|--|

****Product appearance and specifications are subject to change without notice.***

