

Bulk Cat6 Ethernet Cable - 1000 ft. - Solid - CMR-Rated - Black

Product ID: WIR6CMRBK



This bulk Cat6 cable delivers reliable Gigabit network connections, which ensures high-performance capability for your demanding Ethernet applications. The Cat6 cable is riser rated for in-wall installations.

This Category 6 cable has been tested for CMR riser installations, and is ideal for in-wall, between floor and elevator shaft cable runs where CMR fire rating is required.

Each of our cables is manufactured using high-quality copper conductors and they are carefully constructed and tested, to keep Near-End Crosstalk (NEXT) well within acceptable limits.

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet and 4K or 1080p video streaming, using cables that include 23 AWG copper.

The WIR6CMRBK delivers reliable performance and is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Designed for riser installation runs such as in walls, between floors and elevator shafts where CMR fire rating is required
- Deliver data, voice and video over Gigabit networks

Features

- UL Listed CMR Riser Fire Rating

- Supports reliable 550MHz/1Gbps Ethernet network connections
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- ETL verified
- High-quality 23 AWG copper wire

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMR Rated (Riser)

Performance

Maximum Data Transfer Rate	10BASE-T through 1000BASE-T Ethernet
Cable Rating	CAT6 550 MHz

Physical Characteristics

Color	Black
Wire Gauge	23 AWG
Conductor Type	Solid Copper
Cable Length	1000.0 ft [304.9 m]
Product Length	1000.0 ft [304.9 m]
Weight of Product	28.1 lb [12.7 kg]

Packaging Information

Package Length	17.7 in [45 cm]
Package Width	17.7 in [45 cm]
Package Height	8.3 in [21 cm]
Shipping (Package) Weight	30.9 lb [14 kg]

What's in the Box



Included in Package roll of Cat6 cable

****Product appearance and specifications are subject to change without notice.***

