

Bulk Cat6 Ethernet Cable - 1000 ft. - Solid - CMR-Rated - Blue

Produkt ID: WIR6CMRBL



The WIR6CMRBL 1000 ft Cat6 Riser Bulk Cable roll (blue) meets or exceeds all Category 6 specifications to ensure reliable Gigabit network connections, and features a foot-marked jacket that makes it easy to tell how much cable is left on the roll and enables you to measure your cable runs to your exact installation requirements.

Constructed of only top quality materials, the WIR6CMRBL delivers reliable performance and is backed by our Lifetime Warranty.

This Category 6 cable has been tested for CMR riser installations, and is ideal for in-wall, between floor and elevator shaft cable runs where CMR fire rating is required.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 23 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

Certifikat, rapporter och kompatibilitet

Användning

- Can be used in riser installations (in-wall, between floor, elevator shaft, etc.)
- Designed for use with Gigabit networks

Funktioner

- UL Listed CMR Riser Fire Rating
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Constructed with top quality components
- High quality 23 AWG copper wire
- Foot-marked cable

Hårdvara

Garantipolicy	Lifetime
Antal ledare	4 Pair UTP
Kabelmanteltyp	PVC - Polyvinyl Chloride
Brandteknisk klass	CMR-klass (Riser)

Prestanda

Kabelklassificering	CAT6 - 500 MHz
---------------------	----------------

Utseende

Färg	Blå
Tråddimension	23 AWG
Ledningstyp	Solid koppar
Kabellängd	1000.0 ft [304.9 m]
Produktlängd	1000.0 ft [304.9 m]
Produktbredd	0.0 in [0.0 mm]
Produkt höjd	0.0 in [0.0 mm]
Produktvikt	34.1 lb [15.4 kg]

Förpackning

Package Length	18.0 in [45.6 cm]
Package Width	17.6 in [44.8 cm]
Package Height	8.7 in [22.0 cm]
Fraktvikt (förpackning)	31.3 lb [14.2 kg]

Vad det är i lådan

Ingår i paketet	1000 ft Roll of Blue CMR Cat 6 Solid UTP Bulk Cable
-----------------	---

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

