

Bulk Cat6 Ethernet Cable - 1000 ft. - Solid - CMR-Rated - Blue

Product ID: WIR6CMRBL



The WIR6CMRBL 1000 ft Cat6 Riser Bulk Cable roll (blue) meets or exceeds all Category 6 specifications to ensure reliable Gigabit network connections, and features a foot-marked jacket that makes it easy to tell how much cable is left on the roll and enables you to measure your cable runs to your exact installation requirements.

Constructed of only top quality materials, the WIR6CMRBL delivers reliable performance and is backed by our Lifetime Warranty.

This Category 6 cable has been tested for CMR riser installations, and is ideal for in-wall, between floor and elevator shaft cable runs where CMR fire rating is required.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 23 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

Certifications, Reports and Compatibility



Applications

- Can be used in riser installations (in-wall, between floor, elevator shaft, etc.)
- Designed for use with Gigabit networks

Features

- UL Listed CMR Riser Fire Rating
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Constructed with top quality components
- High quality 23 AWG copper wire
- Foot-marked cable

Hardware	Warranty	Lifetime
	Number of Conductors	4 Pair UTP
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Fire Rating	CMR Rated (Riser)
Performance	Cable Rating	CAT6 - 500 MHz
Physical Characteristics	Color	Blue
	Wire Gauge	23 AWG
	Conductor Type	Solid Copper
	Cable Length	1000.0 ft [304.9 m]
	Product Length	1000.0 ft [304.9 m]
	Weight of Product	34.1 lb [15.4 kg]
Packaging Information	Package Length	18.0 in [4.6 cm]
	Package Width	17.6 in [4.5 cm]
	Package Height	9.3 in [2.4 cm]
	Shipping (Package) Weight	29.3 lb [13.2 kg]
What's in the Box	Included in Package	1000 ft Roll of Blue CMR Cat 6 Solid UTP Bulk Cable

**Product appearance and specifications are subject to change without notice.*

