

Bulk Cat 5e Ethernet Cable - 1000 ft. - Solid - CMR-Rated - Blue

Produkt ID: WIRC5ECMR



The WIRC5ECMR Cat5e 350MHz Solid UTP Cable (Blue) is CMR rated for use in walls, conduit, ceilings, etc. and is packaged as a 1000-foot bulk roll. The cable features a blue PVC jacket, which provides both flexibility and durability, while making it easier to color code network cable connections.

Backed by StarTech.com's Lifetime Warranty.

Certifikat, rapporter och kompatibilitet

Användning

- Ideal for network installation at home, office, or educational institution
- CMR rated for use in walls, conduit, ceiling and other vertical applications

Funktioner

- UL Listed CMR Riser Fire Rating
- Rated up to 350Mhz to provide superior performance and bandwidth over the standard 100Mhz Category 5e specifications
- Flexible PVC rated jacket
- 24 AWG solid bare copper conductor

- 4-pair unshielded twisted pair (UTP) cable
- Foot-marked cable

Hårdvara

Garantipolicy	Lifetime
Antal ledare	4 Pair UTP
Kabelmanteltyp	PVC - Polyvinyl Chloride
Brandteknisk klass	CMR-klass (Riser)
Industristandarder	Category 5 CMR

Prestanda

Maximal kabellängd	1000.0 ft [304.9 m]
--------------------	---------------------

Utseende

Färg	Blå
Tråddimension	24 AWG
Ledningstyp	Solid koppar
Kabellängd	1000.0 ft [304.9 m]
Produktlängd	1000.0 ft [304.9 m]
Produktvikt	20.6 lb [9.3 kg]

Förpackning

Package Length	14.0 in [35.5 cm]
Package Width	8.5 in [21.7 cm]
Package Height	13.9 in [35.2 cm]
Fraktvikt (förpackning)	21.0 lb [9.5 kg]

Vad det är i lådan

Ingår i paketet	1000 ft Bulk Roll of Blue CMR Cat5e Solid UTP Cable
-----------------	---

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

