

## Bulk Cat 5e Ethernet Cable - 1000 ft. - Solid - CMR-Rated - Blue

Product ID: WIRC5ECMR



The WIRC5ECMR Cat5e 350MHz Solid UTP Cable (Blue) is CMR rated for use in walls, conduit, ceilings, etc. and is packaged as a 1000-foot bulk roll. The cable features a blue PVC jacket, which provides both flexibility and durability, while making it easier to color code network cable connections.

Backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- CMR rated for use in walls, conduit, ceiling and other vertical applications
- Ideal for network installation at home, office, or educational institution

### Features

- 24 AWG solid bare copper conductor
- 4-pair unshielded twisted pair (UTP) cable
- Flexible PVC rated jacket
- Rated up to 350Mhz to provide superior performance and bandwidth over the standard 100Mhz Category 5e specifications
- UL Listed CMR Riser Fire Rating
- Foot-marked cable

---

Hardware

Warranty

Lifetime

Number of Conductors	4 Pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMR Rated (Riser)
Industry Standards	Category 5
Industry Standards	CMR

---

<b>Performance</b>	Maximum Cable Length	1000.0 ft [304.9 m]
--------------------	----------------------	---------------------

---

<b>Physical Characteristics</b>	Color	Blue
	Wire Gauge	24 AWG
	Conductor Type	Solid Copper
	Cable Length	1000.0 ft [304.9 m]
	Product Length	1000.0 ft [304.9 m]
	Weight of Product	20.6 lb [9.3 kg]

---

<b>Packaging Information</b>	Package Length	14.0 in [3.6 cm]
	Package Width	8.5 in [2.2 cm]
	Package Height	13.9 in [3.5 cm]
	Shipping (Package) Weight	21.0 lb [9.5 kg]

---

<b>What's in the Box</b>	Included in Package	1000 ft Bulk Roll of Blue CMR Cat5e Solid UTP Cable
--------------------------	---------------------	---

---

*\*Product appearance and specifications are subject to change without notice.*

