

Bulk Cat 5e Ethernet Cable - 1000 ft. - Solid - CMR-Rated - Gray

Product ID: WIRC5ECMRGRY



The WIRC5ECMRGRY Cat5e 350MHz Solid UTP Cable (Gray) is CMR rated for use in walls, conduit, ceilings, etc. and is packaged as a 1000-foot bulk roll. The cable features a gray PVC jacket, which provides both flexibility and durability, while making it easier to color code network cable connections.

Backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- CMR rated for use in walls, conduit, ceiling and other vertical applications
- Ideal for network installation at home, office, or educational institution

Features

- 24 AWG solid bare copper conductor
- 4-pair unshielded twisted pair (UTP) cable
- Flexible PVC rated jacket
- Rated up to 350Mhz to provide superior performance and bandwidth over the standard 100Mhz Category 5e specifications
- UL Listed CMR Riser Fire Rating

- Foot-marked cable

Hardware

Warranty	Lifetime
Number of Conductors	4 Pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMR Rated (Riser)
Industry Standards	Category 5 CMR

Performance

Maximum Cable Length	1000.0 ft [304.9 m]
----------------------	---------------------

Physical Characteristics

Color	Gray
Wire Gauge	24 AWG
Conductor Type	Solid Copper
Cable Length	1000.0 ft [304.9 m]
Product Length	1000.0 ft [304.9 m]
Product Width	0.2 in [5 mm]
Product Height	0.2 in [5 mm]
Weight of Product	20.3 lb [9.2 kg]

Packaging Information

Package Quantity	1
Package Length	14.0 in [35.5 cm]
Package Width	14.0 in [35.5 cm]
Package Height	8.5 in [21.5 cm]
Shipping (Package) Weight	21.4 lb [9.7 kg]



**What's in the
Box**

Included in Package	1000 ft Bulk Roll of Gray CMR Cat5e Solid UTP Cable
---------------------	-----------------------------------------------------

****Product appearance and specifications are subject to change without notice.***

