

Bulk Cat6 Ethernet Cable - 1000 ft. - Solid - CMR-Rated - Blue

Product ID: WIRC6CMRBL



This Cat6 500MHz Solid UTP Cable is CMR rated for use in walls, conduit, ceilings, etc. and is packaged as a 1000ft bulk roll. The cable features a blue PVC jacket that provides both flexibility and durability, while making it easier to color code network cable connections.

Backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

Features

- UL Listed CMR Riser Fire Rating
- Compliant to draft 5 of the TIA Category 6 specification
- Packaged in a reelelex box for easy pulling and fewer kinks
- Ripcord allows cable jacket to be removed quickly
- Foot-marked cable

Hardware

Warranty	Lifetime
Number of Conductors	4 Pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMR Rated (Riser)

Performance

Cable Rating	CAT6 - 500 MHz
--------------	----------------

Physical Characteristics

Color	Blue
Wire Gauge	24 AWG
Conductor Type	Solid Copper
Cable Length	1000.0 ft [304.9 m]
Product Length	1000.0 ft [304.9 m]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	28.1 lb [12.8 kg]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	15.0 in [38.0 cm]
Package Height	14.9 in [37.9 cm]
Shipping (Package) Weight	28.1 lb [12.8 kg]

What's in the Box

Included in Package	1 - 1000 ft. Roll of Blue Category 6 CMR Wire Utp
---------------------	---

Warranty Information

Warranty

Lifetime

****Product appearance and specifications are subject to change without notice.***