

Bulk Cat6 Ethernet Cable - 1000 ft. - Stranded - CM-Rated for In-Wall Use - Green

Product ID: WIRC6PATGNRL



This 1000ft roll of (green) Stranded Category 6 cable is the perfect way to connect your emerging gigabit network. Our Stranded Cat 6 cable is expertly designed and constructed, and backed by lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Can be used in any 10Base-T, 100Base-TX or 1000Base-TX (Gigabit Ethernet) network
- Can be used in home, office and other environments

Features

- Available in various colors for easy identification and color-coding
- Lifetime Warranty

Hardware

Warranty

Lifetime

	Number of Conductors	4 pair UTP
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Fire Rating	CM Rated
Performance		
	Cable Rating	CAT6 - 500 MHz
Physical Characteristics		
	Color	Green
	Wire Gauge	24 AWG
	Conductor Type	Stranded Copper
	Cable Length	1000.0 ft [304.9 m]
	Product Length	1000.0 ft [304.9 m]
	Weight of Product	29.3 lb [13.3 kg]
Packaging Information		
	Package Quantity	1
	Package Length	14.5 in [36.8 cm]
	Package Width	8.7 in [22.2 cm]
	Package Height	15.5 in [39.4 cm]
	Shipping (Package) Weight	28.9 lb [13.1 kg]
What's in the Box		
	Included in Package	1 - 1000 ft Green Cat 6 Stranded UTP Patch Cable

****Product appearance and specifications are subject to change without notice.***