

Bulk Cat6 Ethernet Cable - 1000 ft. - Stranded - CM-Rated for In-Wall Use - Gray

Produkt ID: WIRC6PATGRRL



This 1000ft roll of Stranded Category 6 cable is the perfect way to connect your emerging gigabit network. Our Stranded Cat 6 cable is expertly designed and constructed, and backed by lifetime warranty.

Certifikat, rapporter och kompatibilitet

Användning

- Can be used in any 10Base-T, 100Base-TX or 1000Base-TX (Gigabit Ethernet) network
- Can be used in home, office and other environments

Funktioner

- Available in various colors for easy identification and color-coding

Hårdvara

Garantipolicy	Lifetime
Antal ledare	4 pair UTP
Kabelmanteltyp	PVC - Polyvinyl Chloride

	Brandteknisk klass	CM-klass
<hr/>		
Prestanda	Kabelklassificering	CAT6 - 500 MHz
<hr/>		
Utseende	Färg	Grå
	Tråddimension	24 AWG
	Ledningstyp	Tvinnad koppar
	Kabellängd	1000.0 ft [304.9 m]
	Produktlängd	1000.0 ft [304.9 m]
	Produktvikt	29.3 lb [13.3 kg]
<hr/>		
Förpackning	Package Length	8.6 in [21.8 cm]
	Package Width	14.9 in [37.8 cm]
	Package Height	15.2 in [38.5 cm]
	Fraktvikt (förpackning)	29.3 lb [13.3 kg]
<hr/>		
Vad det är i lådan	Ingår i paketet	1000ft Roll Grey Stranded Cat 6 Patch Cable
<hr/>		

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

