

Bulk Cat6 Ethernet Cable - 1000 ft. - Stranded - CM-Rated for In-Wall Use - Gray

Product ID: WIRC6PATGRRL



This 1000ft roll of Stranded Category 6 cable is the perfect way to connect your emerging gigabit network. Our Stranded Cat 6 cable is expertly designed and constructed, and backed by lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Can be used in any 10Base-T, 100Base-TX or 1000Base-TX (Gigabit Ethernet) network
- Can be used in home, office and other environments

Features

- Available in various colors for easy identification and color-coding

Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CM Rated

Performance

Cable Rating	CAT6 - 500 MHz
--------------	----------------

Physical Characteristics

Color	Gray
Wire Gauge	24 AWG
Conductor Type	Stranded Copper
Cable Length	1000.0 ft [304.9 m]
Product Length	1000.0 ft [304.9 m]
Weight of Product	29.3 lb [13.3 kg]

Packaging Information

Package Length	8.6 in [21.8 cm]
Package Width	14.9 in [37.8 cm]
Package Height	15.2 in [38.5 cm]
Shipping (Package) Weight	29.3 lb [13.3 kg]

What's in the Box

Included in Package	1000ft Roll Grey Stranded Cat 6 Patch Cable
---------------------	---

****Product appearance and specifications are subject to change without notice.***

