

Bulk Cat6 Ethernet Cable - 1000 ft. - Stranded - CM-Rated for In-Wall Use - White

Produkt-ID: WIRC6PATWHRL



This 1000ft roll of Stranded Category 6 cable is the perfect way to connect your emerging gigabit network. Our Stranded Cat 6 cable is expertly designed and constructed, and backed by lifetime warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Can be used in home, office and other environments
- Can be used in any 10Base-T, 100Base-TX or 1000Base-TX (Gigabit Ethernet) network

Merkmale

- Available in various colors for easy identification and color-coding

Hardware

Garantiebestimmungen Lifetime

	Anzahl von Leitern	4 pair UTP
	Typ der Kabelummantelung	PVC - Polyvinyl Chloride
	Feuerwiderstandssklasse	Ausgelegt gemäß CMe
Leistung	Kabelnennwerte	CAT6 - 500 MHz
Physische Eigenschaften	Farbe	Weiß
	Drahtstärke	24 AWG
	Leitungstyp	Feindrähtiges Kupfer
	Kabellänge	1000.0 ft [304.9 m]
	Produktlänge	1000.0 ft [304.9 m]
	Produktgewicht	29.3 lb [13.3 kg]
Verpackungsinformationen	Paketmenge	1
	Paketlänge	14.9 in [37.8 cm]
	Paketbreite	8.7 in [22.0 cm]
	Pakethöhe	15.1 in [38.4 cm]
	Versandgewicht (Verpackung)	29.7 lb [13.5 kg]
Verpackungsinhalt	Im Paket enthalten	1 - 1000ft Roll White Stranded Cat 6 Patch Cable
Garantieinformationen	Warranty	Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.