

Bulk Cat6 Ethernet Cable - 1000 ft. - Stranded - CM-Rated for In-Wall Use - Yellow

Product ID: WIRC6PATYLRL



This 1000ft roll of (yellow) Stranded Category 6 cable is the perfect way to connect your emerging gigabit network. Our Stranded Cat 6 cable is expertly designed and constructed, and backed by lifetime warranty.

## Certifications, Reports and Compatibility

## Applications

- Can be used in any 10Base-T, 100Base-TX or 1000Base-TX (Gigabit Ethernet) network
- Can be used in home, office and other environments

## Features

- Available in various colors for easy identification and color-coding
- Lifetime Warranty

---

### Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CM Rated

---

**Performance**

Cable Rating	CAT6 - 500 MHz
--------------	----------------

---

**Physical Characteristics**

Color	Yellow
Wire Gauge	24 AWG
Conductor Type	Stranded Copper
Cable Length	1000.0 ft [304.9 m]

---

**Packaging Information**

Package Length	8.5 in [21.6 cm]
Package Width	14.9 in [37.8 cm]
Package Height	15.0 in [38 cm]
Shipping (Package) Weight	28.1 lb [12.7 kg]

---

**What's in the Box**

Included in Package	1000 ft Yellow Cat 6 Stranded UTP Patch Cable
---------------------	---

---

*\*Product appearance and specifications are subject to change without notice.*

