

6ft (1.8m) Heavy Duty Extension Cord, Twist-Lock NEMA L6-20P to C19, 20A 250V, 12AWG, Black Extension Cable, Heavy Gauge Power Cable, TAA Compliant, UL Listed

Product ID: ZA16-2600-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Heavy Duty power cord supports high-powered equipment and PDUs

Features

- **HEAVY DUTY POWER CORD:** 6ft (1.8m) Heavy Duty Power Cord with Twist-Lock NEMA L6-20P to IEC 60320 C19 connector is suitable for high-power equipment; Locking L6-20 plug securely attaches to an outlet or power source; Indoor Use; Rated to carry 250V at 20A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 6ft (1.8m); TAA Compliant; Twist-Lock NEMA L6-20P to IEC 60320 C19; 12AWG; 250V 20A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.44in (11.2mm)
- **COMPATIBILITY:** Heavy Duty Power Cord NEMA L6-20P plug works with high power PDUs and power supplies; IEC C19 connector works with servers, switches, and rackmount appliances; Replacement PDU power cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

Connector(s)

Connector A	1 - NEMA L6-20 Power (North America, Locking)
Connector B	1 - IEC 60320 C19 Power

Power

Input Voltage	250V AC
Input Current	20A

	Output Current	20A
Environmental		
	Operating Temperature	-20 to 105C (-4 to 221F)
	Storage Temperature	-20 to 105C (-4 to 221F)
	Humidity	0% to 65% RH
Physical Characteristics		
	Color	Black
	Wire Gauge	12 AWG
	Cable Length	6.0 ft [1.8 m]
	Cable OD	0.4 in [11.2 mm]
	Product Length	6.0 ft [1.8 m]
	Product Width	1.5 in [3.9 cm]
	Product Height	1.5 in [3.9 cm]
	Weight of Product	1.1 lb [0.5 kg]
Packaging Information		
	Package Length	10.0 in [25.4 cm]
	Package Width	3.9 in [9.8 cm]
	Package Height	2.3 in [5.8 cm]
	Shipping (Package) Weight	1.2 lb [0.5 kg]
What's in the Box		
	Included in Package	1 - 6ft C19 to NEMA L6-20 Heavy-Duty Power Cord
Warranty Information		
	Warranty	Lifetime

**Product appearance and specifications are subject to change without notice.*