

100W USB-C Laptop Charger with 1.5m Tethered USB-C Cable, Power Adapter Brick for Dell, XPS, HP ProBook, MacBook Pro, Microsoft Surface Pro

Product ID: 1100LE-USB-C-CHARGER



This USB-C power adapter delivers up to 100W of Power Delivery 3.0/2.0 power with broad voltage support (5V, 9V, 12V, 15V, 20V), letting you quickly and safely charge a wide range of devices, replacing multiple chargers with one dependable solution.

Designed for use with popular USB-C devices including Dell Pro/Plus, HP, HP ProBook, MacBook Pro, and Microsoft Surface Pro, this charger includes a 1.8m power cord and a 1.5m tethered USB-C cable for extended reach and reliable, always-ready power, ideal for mobile or hybrid work.

Built to keep both users and devices protected, it is ETL Safety Listed (IEC 623681) and CE/FCC/ICES EMC certified, with overvoltage, current, and temperature protection. Its efficient design meets DOE Level VI standards for energy efficiency.

Packaged with sustainability in mind, the recyclable brown box minimizes environmental impact and is compact to prevent product movement or damage during transport.

Certifications, Reports and Compatibility



Applications

Features

- **Powerful, Fast, Universal Charging:** Delivers up to 100W of USB-C PD 3.0/2.0 power with broad voltage support (5V, 9V, 12V, 15V, 20V) to quickly and safely charge devices from smartphones to laptops, with a single, versatile charger
- **Universal USB-C Charging for Leading Brands:** For use with Dell Pro/Plus, HP ProBook, Apple MacBook Pro, and Microsoft Surface Pro; Includes a 1.8m power cord and a 1.5m tethered USB-C cable for extended reach and reliable, always-ready power
- **Safe, Reliable and Efficient:** ETL Safety Listed (IEC 62368-1) and CE/FCC/ICES EMC certified with over-voltage, current, and temp protection to keep both users and devices safe; Efficient design meets DOE Level VI standards
- **Reduces Packaging Waste:** Ships in a recyclable brown box with a cardboard twist tie; Compact packaging protects the product in transit while minimizing environmental impact
- **The IT Pro's Choice:** Our power adapters offer a long-lasting, eco-conscious solution as manufacturers increasingly exclude chargers from new devices; Thoroughly tested in our Innovation Lab to ensure enterprise-grade reliability and operational safety

General

UPC	065030922029
Warranty	2 Years

Power

Input Voltage	100 - 240 AC
Input Current	2.0A
Output Voltage	5V DC
	9V DC
	12V DC
	15V DC
	20V DC
Output Current	5
Plug Type	USB Type-C (24 pin) USB Power Delivery Only
Power Consumption	100W

Physical & Environmental

Color	Black
Material	Plastic

Cable Length	5.0 ft [1.5 m]
Product Length	3.5 in [89.5 mm]
Product Width	2.6 in [67 mm]
Product Height	1.0 in [26 mm]
Weight of Product	11.6 oz [329 g]
Operating Temperature	0C to 25C (32F to 77F)
Storage Temperature	-20C to 80C (-4F to 176F)
Humidity	Operating 10% to 90% Storage 30% to 90%

Hardware

Number of Ports	1
Rack-Mountable	No
Industry Standards	TUV Safety Listed (IEC 62368-1)
	USB Power Delivery 3.0

Packaging & In-the-Box

Included in Package	1 - Adapter Brick
	1 - AC Power Cable (EU)
	1 - Product Documentation
Package Width	4.1 in [10.4 cm]
Package Depth	6.6 in [16.8 cm]
Package Height	2.8 in [72 mm]
Shipping (Package) Weight	18.3 oz [519 g]

Connector(s)

Connector 1 (Quantity)	1
Connector 1	CEE 7/16 (250V AC, 2.5A)
Connector 2 (Quantity)	1

Connector 2

USB-C (100W PD Only)

****Product appearance and specifications are subject to change without notice.***