

10ft (3m) Power Extension Cord, Locking C14 to C13, PDU Power Cord, 10A 250V, 18AWG, AC Power Cable Extension, TAA Compliant, UL Listed

Product ID: C14LC1318G10ABK10FT



The IT Pro's Choice

StarTech's power cables are designed by and for IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using ETL listed components
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions
- Backed for life with free lifetime 24/5 multi-lingual technical assistance

StarTech is trusted throughout the IT ecosystem and used by over 90% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

Features

- **Deliver Reliable Power:** Connect servers, network equipment, and rack-mounted hardware to a PDU using this 10ft (3m) Locking C14 to C13 power extension cord; Built with 18AWG 100% copper wire and rated for up to 250V at 10A
- **Minimize Power Interruptions:** Maintain uptime for mission-critical equipment with a locking C14 connector that resists vibration, tension, and accidental unplugging; Reduces power loss risk when extending PDU connections
- **Ensure Certified Electrical Safety:** Support professional deployments with a UL Listed power cord featuring a VW-1 flame-rated jacket; Flexible SJTW jacket enables clean and safe routing through dense racks and cable trays
- **Replace Aging Power Cables:** Eliminate unreliable power cords with a locking cable that stays securely connected; IEC 60320 C14 connects to rackmount PDUs and C13 supports servers, switches, and workstations; TAA Compliant
- **The IT Pro's Choice:** Our power cords are rigorously tested in our in-house Innovation Lab for reliable performance, durable construction, and compatibility across a variety of devices; Backed by free lifetime 24/5 multi-lingual technical assistance

General

UPC	065030927581
Warranty	Lifetime

Power

Input Voltage	250V AC
Input Current	15A

Physical & Environmental

Color	Black
Connector Style	Straight
Wire Gauge	14 AWG
Cable Length	10.0 ft [3.0 m]
Cable OD	0.3 in [7.8 mm]

Product Length	10.1 ft [3.1 m]
Product Width	0.5 in [12.5 mm]
Product Height	0.8 in [20.7 mm]
Weight of Product	11.1 oz [314 g]
Operating Temperature	-20 to 105C (-4 to 221F)
Storage Temperature	-20 to 105C (-4 to 221F)
Humidity	0% to 65% RH

Hardware

Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC (Polyvinyl Chloride)
Fire Rating	VW-1 (Vertical-Wire Flame Test)

Packaging & In-the-Box

Included in Package	1 - 10ft Locking C14 to C13 Power Cord
Package Width	5.4 in [13.8 cm]
Package Depth	14.8 in [37.5 cm]
Package Height	2.0 in [50 mm]
Shipping (Package) Weight	10.2 oz [290 g]

Connector(s)

Connector 1 (Quantity)	1
Connector 1	IEC C14 (250V AC, 10A)
Connector 2 (Quantity)	1
Connector 2	IEC C13 (250V AC, 10A)

****Product appearance and specifications are subject to change without notice.***