

24 Port 1U Blank Keystone Patch Panel with Cable Management Bar, Rackmount Patch Panel for RJ45 UTP Ethernet Network Jacks

Product ID: C6PANELUTP241UCM



Deploy multiple Ethernet cable terminations in rack-mounted network setups, using this 24-Port 1U Blank Keystone Patch Panel with Cable Management Bar. It is designed for high-density installations such as wiring closets and data centers, where modular port configuration and clean cable routing are key to long-term serviceability.

The 1U keystone patch panel supports standard unshielded (UTP) RJ45 keystone jacks, matching Cat5e or Cat6 network cabling. Numbered port labels along the front panel provide quick identification for maintenance and troubleshooting.

The steel housing features a black powder-coated finish for scratch resistance and long-term durability. An integrated cable management bar with tie-down slots reduces cable strain and maintains a tidy setup, improving passive airflow and ease of access when troubleshooting.

Certifications, Reports and Compatibility



Applications

- For installation in standard 19in network racks and cabinets
- Install Cat5e and Cat6 keystone jacks without punch down tools. Quickly swap jacks as needed for configuration and troubleshooting
- Clearly numbered keystone ports make it easy to identify your cable runs

Features

- **Customize Patch Panel Layout:** Install up to 24 UTP RJ45 keystone jacks for high-performance networking; 1U blank keystone panel features a toolless, modular design with clearly numbered ports; Ideal for modular and scalable network builds
- **Route Cables Cleanly:** Neatly organize cabling with the rear cable management bar, featuring individual U-shaped cable guides and side anchor slots for attaching cable ties; Maintain a tidy rack layout for improved airflow, easy access and troubleshooting
- **Streamline Network Terminations:** Install Cat8/Cat6A/Cat6/Cat5e UTP keystone jacks without punch down tools; Quickly replace jacks as needed to maintain service continuity and minimize downtime
- **Mount in Any Standard Rack:** Includes mounting screws and cage nuts for installation into any 19in rack or wall-mount enclosure; Toolless keystone slots support fast, flexible deployment during upgrades or rollouts
- **The IT Pro's Choice:** Designed for reliability in edge and on-prem deployments, our networking solutions are lab-tested and field-proven for seamless integration and maximum uptime; Backed by free lifetime 24/5 multi-lingual technical assistance

General

UPC	065030911726
Warranty	2 Years

Physical & Environmental

Color	Black
Material	Steel
Product Length	19.0 in [48.3 cm]
Product Width	5.4 in [13.8 cm]
Product Height	1.7 in [44.3 mm]
Weight of Product	17.5 oz [496 g]
Operating Temperature	-10°C to 60°C (14°F to 140°F)
Storage Temperature	-40°C to 70°C (-40°F to 158°F)
Humidity	85%

Packaging & In-the-Box

Included in Package	1 - Patch Panel
---------------------	-----------------

1 - Cable Manager

1 - Product Documentation

1 - Set of Screws and Nuts

Package Width 2.8 in [70 mm]

Package Depth 20.3 in [51.5 cm]

Package Height 2.4 in [60 mm]

Shipping (Package)
Weight 25.9 oz [733 g]

****Product appearance and specifications are subject to change without notice.***