

15ft Purple Slim CAT6 Ethernet Cable, Snagless, 100W PoE, UTP, LSZH, 28AWG Pure Bare Copper Wire, Slim RJ45 Network Patch Cord w/Strain Reliefs, Individually Tested

Produkt-ID: N6PAT15PLS



This slim CAT6 cable meets all Category 6 patch cable specifications to deliver a reliable Gigabit and Power over Ethernet (PoE) network connection in high-density network installations.

The Slim Cat6 Patch Cord is 36% thinner than standard Cat6 Ethernet cables, enabling greater airflow and heat dissipation in confined spaces. The Slim Cat6 Ethernet cable is also more flexible, for easier cable routing in crowded network racks and patch panels.

This cable features snagless connectors that protect the RJ45 clips during installation, reducing snags or breakage when routing through narrow gaps or in between devices.

The Slim Cat6 Cable features 50-micron gold RJ45 contacts that ensure a precise fit to minimize wear and signal loss. The 4-pair Unshielded Twisted Pair (UTP) construction utilizes 28AWG Pure Bare Copper Wire for improved conductivity and low resistance. The flexible Low Smoke Zero Halogen (LSZH) flame-retardant jacket emits low smoke and toxic fumes when exposed to extreme heat or in the event of a fire. This enables safer installations in poorly-ventilated areas including some industrial settings, self-contained environments such as trains and aircraft, as well as residential settings where compliance with building codes must be considered.

Each cable is individually tested using a Fluke® DSX2-8000 CableAnalyzer™ to meet ANSI/TIA-568.2-D Category 6 specifications, ensuring consistent signal integrity with minimal Near-End Crosstalk (NEXT) and Return Loss (RL). Reliably deliver up to 100W of PoE++ to power a remote networking devices, including PoE switches and boardroom cameras. This Slim Cat6 Patch Cable complies with IEEE 802.3bt Type 4 PoE++ specifications.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Route slim Cat6 cables to enable greater airflow and heat dissipation in confined spaces. Flexible Low Smoke Zero Halogen (LSZH) jacket is ideal for routing in crowded rackmount setups and patch panels.

Merkmale

- Platzsparende Verkabelung: Schlankes Cat6 Kabel ist 36 Prozent dünner als Standard Cat6 Leitungen; erhöht Flexibilität und erleichtert Verlegung in dichten IT Umgebungen für strukturierte und effiziente Installation
- Für Leistung gebaut: Unterstützt 10Gbps Geschwindigkeit und 100W PoE IEEE 802.3bt Typ 4 mit 28AWG reinem Kupferdraht und 50 Mikron vergoldeten Kontakten für zuverlässige Signalqualität; flexibler LSZH Mantel hält engen Biegeradien stand
- Auf Zuverlässigkeit getestet: Entspricht ANSI TIA 568 C.2 Standards für garantierte Cat6 Leistung bis 250MHz; Einzeln getestet für minimales Near-End Crosstalk (NEXT) und Return Loss (RL)
- Zugang und Luftstrom verbessern: Schlanke Cat6 Kabel erleichtern Wartung und verbessern den Luftstrom zwischen Geräten; verbinden zuverlässig PoE Geräte wie IP oder Konferenzkameras; LSZH Mantel erzeugt im Brandfall wenig Rauch
- Die Wahl der IT Profis: Entwickelt für Zuverlässigkeit in Edge und On Prem Umgebungen; unsere Netzkabel sind getestet für nahtlose Integration und maximale Betriebszeit; unterstützt durch kostenlosen lebenslangen 24-5 mehrsprachigen Support

Allgemein

UPC	065030913102
Warranty	Lifetime

Strom

Stromversorgung (Power Delivery)	100W
-------------------------------------	------

Physische Eigenschaften & Umgebung

Farbe	Violett
Leiterquerschnitt	28 AWG

Leitertyp	Stranded Copper
Cable Length	15.0 ft [4.6 m]
Kabelaußendurchmesser	0.1 in [3.6 mm]
Product Length	15.1 ft [4.6 m]
Product Width	0.4 in [11.3 mm]
Product Height	0.5 in [13.6 mm]
Weight of Product	2.9 oz [82 g]
Betriebstemperatur	10°C ~ 60°C (50°F to 140°F)
Lagertemperatur	-20°C ~ 60°C (-4°F to 140°F)
Luftfeuchtigkeit	10% ~ 80%

Leistung

Maximale Datenübertragungsrate	10 Gbps
Kabelklassifizierung	CAT6 - 250 MHz

Hardware

Anzahl der Leiter	4 Pair UTP
Steckverbinder-Kontakt beschichtung	Gold
Kabelmantelmaterial	LSZH (Low Smoke Zero Halogen)
Kabeltyp	Snagless
Verkabelungsstandard	TIA/EIA-568-B.1-2001 T568B

Verpackung & Lieferumfang

Im Lieferumfang enthalten	1 - Schlankes Cat6 Ethernet-Kabel - LSZH
Package Width	7.9 in [20 cm]

Package Depth	8.7 in [22 cm]
Package Height	0.4 in [10 mm]
Shipping (Package) Weight	3.4 oz [96.2 g]

Steckverbinder

Anschluss 1 (Anzahl)	1
Anschluss 1	RJ-45
Anschluss 2 (Anzahl)	1
Anschluss 2	RJ-45

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.