

4.5m (15ft) Power Extension Cord, C14 to C13 PDU Power Cord, 10A 250V, 14AWG, AC Power Cable for PDU/Power Supply, KEMA-KEUR Certified

Product ID: PXTC13C141415FEU



This certified C14 to C13 power extension cord extends connections from a PDU or UPS to servers, monitors, printers, and other IT equipment. The 15ft (4.5m) length provides extra reach, enabling flexible hardware placement in server rooms, network closets, and workstations.

Engineered to meet strict European safety regulations, this power cord is KEMA-KEUR certified and built to H05VV-F classification for EU power standard compliance. The VW-1 flame rating enhances fire safety, and is suitable for environments where fire resistance must be considered.

The 15ft length facilitates added distance between devices and power sources, allowing easier positioning of equipment without being limited by outlet locations.

Built for longevity, this C14 to C13 power extension cord features a fully molded design and is made from 100% copper wire. It is rated for 250V at 10A with 14AWG conductors, ensuring reliable and stable power transmission.

Certifications, Reports and Compatibility



Applications

- Establish a reliable power connection from your server to a PDU

Features

- **UNIVERSAL EXTENSION CORD:** This C14 to C13 power extension cord allows you to extend connections from a PDU or UPS to servers, monitors, printers, and other IT or AV equipment; 15ft (4m) length provides extra reach for flexible equipment placement
- **DURABLE AND RELIABLE:** Extra-long (replacement) extension cord features a fully molded design and 100% copper wire for a secure and reliable connection; Rated for 250V at 10A with 14AWG conductors for safe and efficient operation
- **CERTIFIED FOR SAFETY:** KEMA-KEUR certified to meet EU safety regulations; H05VV-F cable class ensures adherence to European power standards, while the VW-1 fire rating enhances safety
- **SPECS:** 4.5-meter (15-foot) AC Power Cord; IEC 60320 C14 to IEC 60320 C13; KEMA-KEUR certified for EU; H05VV-F Cable Class; 14AWG; 250V 10A (max); Jacket Material: PVC; Temp Range: 3C to 60C; Cable O.D.: 9.25mm (0.36in)
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

General

UPC	065030920506
Warranty	Lifetime

Power

Input Voltage	250 AC
Input Current	10A

Physical & Environmental

Color	Black
Wire Gauge	14 AWG
Cable Length	15.0 ft [4.6 m]
Cable OD	0.4 in [9.3 mm]
Product Length	15.0 ft [4.6 m]
Product Width	1.1 in [28.7 mm]
Product Height	1.0 in [25 mm]
Weight of Product	13.5 oz [383 g]
Operating Temperature	0 to 70 (32°F to 158°F)

Storage Temperature	-15 to 70 (5°F to 158°F)
Humidity	30% - 90%

Hardware

Cable Jacket Material	PVC (Polyvinyl Chloride)
Fire Rating	VW-1 (Vertical-Wire Flame Test)
Cable Type	SJT

Packaging & In-the-Box

Included in Package	1 - 4.5m C14 to C13 Power Extension Cord
Package Width	5.7 in [14.5 cm]
Package Depth	11.4 in [29 cm]
Package Height	2.0 in [50 mm]
Shipping (Package) Weight	13.4 oz [380 g]

Connector(s)

Connector 1 (Quantity)	1
Connector 1	IEC C13 (250V AC, 10A)
Connector 2 (Quantity)	1
Connector 2	IEC C14 (250V AC, 10A)

****Product appearance and specifications are subject to change without notice.***