

3ft (1m) USB-A to USB-C Charging Cable, Charge & Sync, 3A, USB 2.0, TPE Jacket - White USB Charging Cord

Product ID: USB2AC1MNCWHE



Charge a USB Type-C mobile device or transfer files to a USB-A host computer with this high-quality USB-A to Type-C cable. The USB-A to USB-C cable supports fast charging with up to 15W and 3A output and offers reliable USB 2.0 transfer speeds of up to 480Mbps, making it ideal for general everyday use.

Designed for frequent or daily use, the USB-A to USB-C Charger Cable features a rugged TPE outer jacket for increased wear resistance. Its flexible strain relief and nickel-plated connectors are designed to withstand over 10,000 insertion cycles, enhancing its durability and longevity.

The 1m (3.3ft) USB Charging Cable is the ideal length for desk workstations or portable charging on-the-go.

Facilitating up to 3A of output, the USB-C Charger Cord can fast-charge a smartphone or tablet. To use, connect the cable from a USB-C device to a USB-A wall charger.

Certifications, Reports and Compatibility



Applications

- Charge and sync a USB-C device from an available USB-A port on a laptop or desktop computer
- Charge your USB-C devices using a USB-A wall charger, car charger or power bank

Features

- **USB-A TO USB-C CHARGING:** High quality USB-A to Type-C cable delivers 3A output for fast charging portable USB-C devices; Connect this cable to a USB-A wall charger, power bank, or charge/access your phone/tablet from a USB-A host
- **QUALITY CONSTRUCTION:** Nickel-plated connectors rated beyond 10,000 insertion cycles; Robust strain reliefs with 8mm bend radius; Durable TPE outer jacket is non-toxic, halogen-free and RoHS compliant; Aluminum braided shield for enhanced EMI protection
- **APPLICATIONS:** Ideal for fast charging phones and other small peripherals; Supports USB 2.0 (480Mbps) for general use, including file transfer and device synchronization when connected to a USB-A host computer or external storage
- **PERFORMANCE:** 15W/3A Fast Charge; USB 2.0 (480Mbps); Length: 1-meter (3.3-foot); Color: White; O.D.: 0.12in (3.0mm); Jacket: TPE w/Aluminum Braided Shield; NOTE: USB-C video (DP Alt Mode) is not supported
- **COMPATIBILITY:** Compatible with a wide range of USB-C devices including iPhone 15 [Plus/Pro/Max] and up, Samsung Galaxy S8 & up, Google Pixel, USB-C portable monitors Asus ZenScreen/ProArt, iPad Pro, MacBook Air/Pro, Surface Book, and more

General

UPC 065030911870

Warranty Lifetime

Special Notes / Requirements

Special Notes Does not support USB Type-C DisplayPort Alternate Mode (DP Alt Mode)

Power

Power Delivery 15W

Input Current 3A

Physical & Environmental

Color White

Material Polyamide Resin

Connector Style Straight

Wire Gauge 24/32 AWG

Cable Length 3.3 ft [1 m]

Cable OD 0.1 in [3.0 mm]

Product Length	3.3 ft [1.0 m]
Product Width	0.6 in [15.8 mm]
Product Height	0.5 in [12.0 mm]
Weight of Product	0.7 oz [21.0 g]
Operating Temperature	-10 to 60 (14°F to 140°F)
Storage Temperature	-20 to 70 (-4°F to 158°F)
Humidity	5%~85%

Performance

Insertion Rating	Rated over 10,000 insertion cycles
MTBF	Rated over 10,000 insertion cycles

Hardware

Active or Passive Adapter	Passive
Connector Plating	Nickel
Cable Jacket Material	TPE (Thermoplastic Elastomer)
Cable Shield Material	Aluminum-Mylar Foil with Braid

Packaging & In-the-Box

Included in Package	1 - 1m USB-A to USB-C Cable - M/M
Package Width	5.0 in [12.8 cm]
Package Depth	8.7 in [22 cm]
Package Height	0.3 in [8 mm]
Shipping (Package) Weight	0.9 oz [26 g]

Connector(s)

Connector 1 (Quantity)	1
Connector 1	USB-A (480Mbps, 2.5W)
Connector 2 (Quantity)	1

Connector 2

USB-C (480Mbps, 2.5W)

****Product appearance and specifications are subject to change without notice.***