




































Drive Duplicators & Erasers









































StarTech.com drive duplicators and erasers are performance tested for reliability with all major drive & file formats, and supported interfaces including IDE, SATA, and M.2.



With our **standalone erasers & duplicators**, simply select your settings, and go. **No host system, and no additional software required.**

 Erase  Duplicate  Dock

	Drive Quantity	Compatibility	Functionality	Host Connection	Duplication Speeds	Modes	Duplicate / Erase Quantity	Additional Features	Product #
	2	SATA 2.5" / 3.5"	 	USB-A / USB-C (10 Gbps)	28 GB/min	 1	Single	4Kn	SDOCK2U313R
	2	SATA 2.5" / 3.5"	 	USB-A (5 Gbps) / eSATA	22 GB/min	 1	Single	4Kn	SDOCK2U33RE
	2	SATA 2.5" / 3.5"	  	USB-A (5 Gbps)	11 GB/min	 1  1	 1  up to 2	4Kn	SATDOCK2REU3
	4	SATA 2.5" / 3.5"	  	USB-A (5 Gbps) / eSATA	4.2 GB/min	 1  2	 up to 3  1	IDE Hard Drive Adapter	SATDOCK4U3RE
	6	SATA 2.5" / 3.5"	  	USB-A (5 Gbps) / eSATA	7 GB/min	 1  4	Up to 5	2x USB Fast Charge	SATDOCK5U3ER
	2	M.2 SATA M.2 NVMe SATA 2.5" / 3.5"	 	Standalone	7.5 GB/min	 4  6	Single	—	SM2DUPE11

	Drive Quantity	Compatibility	Functionality	Host Connection	Duplication Speeds	Modes	Duplicate / Erase Quantity	Additional Features	Product #
	3	USB Flash Drives		Standalone	1.5 GB/min	 2  3	Up to 2	—	USBDUP12
	6	USB Flash Drives		Standalone	1.5 GB/min	 2  3	Up to 5	—	USBDUP15
	8	USB Flash Drives		Standalone	1.5 GB/min	 2  3	Up to 7	—	USBDUPE17
	16	USB Flash Drives		Standalone	1.5 GB/min	 2  3	Up to 15	—	USBDUPE115
	2	SATA 2.5" / 3.5"		Standalone	14 GB/min	 4  5	 1  up to 2	—	SATDUP11
	2	SATA 2.5" / 3.5" USB Flash Drives		Standalone	18 GB/min	 4  4	 1  up to 2	—	SU2DUPERA11
	2	SATA 2.5" / 3.5" SAS 2.5" / 3.5"		Standalone	13 GB/min	 4  6	 1  up to 2	—	SATSASDUPE11
	2	SATA 2.5" / 3.5"		Standalone	6 GB/min	 4	Single	Disk Image Manager	SATDUP11IMG
	4	SATA 2.5" / 3.5"		USB-A (5 Gbps)	—	 7	Up to 4	RS232 Printer Connection	SATERASER4
	1	SATA 2.5" / 3.5"		USB-A (5 Gbps)	—	 7	Single	RS232 Printer Connection	SDOCK1EU3P
	1	SATA 2.5" / 3.5"		USB-A (5 Gbps)	—	 7	Single	4kn RS232 Printer Connection	SDOCK1EU3P2