Cat5e Patch Cable with Snagless RJ45 Connectors - 25 ft, Yellow

Product ID: 45PATCH25YL

This 25-foot Cat5e cable meets or exceeds all Category 5e cable specifications to ensure reliable Ethernet network connections. Plus, the cable features a durable yellow PVC jacket that enables you to color code your network cable runs as needed.

For easier cable runs, the snagless connectors protect the cable's RJ45 clips during installation, making them less likely to snag or break. This ensures a sturdy connection by preventing the cable from becoming loose from the port.

The cable features moulded boots that offer connector strain relief, by stopping the RJ45 connector termination points from bending at sharp angles, and reducing the risk of damage to the cable, which could decrease network performance.

Get the highest value for your cable investment with our Cat 5e cables, each one manufactured using high-quality copper conductors.

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet, using cables that include 24 AWG copper.

Rely on our RJ45 connectors to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

The 45PATCH25YL is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility

RoHS Compliant

Applications

• Designed for use with Fast Ethernet networks

• Connect between computers, hubs, switches, print servers and patch panels

• Connect a workstation to an RJ45 wall outlet

• Extend the reach of your Ethernet network devices by 25 ft

Features

• Prevent cable damage with moulded RJ45 connectors that also offer strain relief

• Create secured connections with snagless clips that protect the connectors during installation

• Guaranteed reliability with a lifetime warranty

• Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits

Hardware		
	Warranty	Lifetime
	Number of Conductors	4 pair UTP
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Fire Rating	CM Rated
	Cable Type	Snagless
Performance		
	Cable Rating	CAT5e - 350 MHz
Connector(s)		
	Connector A	1 - RJ-45
	Connector B	1 - RJ-45
Physical Characteristics		
	Color	Yellow
	Wire Gauge	24 AWG
	Conductor Type	Stranded Copper

	Cable Length	25.0 ft [7.6 m]
	Product Length	25.0 ft [7.6 m]
	Product Width	0.5 in [1.2 cm]
	Product Height	0.5 in [1.4 cm]
	Weight of Product	8.8 oz [248.0 g]
Packaging Information		
	Package Quantity	1
	Package Length	13.0 in [33.0 cm]
	Package Width	10.0 in [25.5 cm]
	Package Height	1.0 in [2.5 cm]
	Shipping (Package) Weight	9.3 oz [264.0 g]
What's in the Box		
	Included in Package	1 - 25 ft. Cat5e Patch Cable - Yellow

Product appearance and specifications are subject to change without notice.