

Extreme Networks 10050 Compatible SFP Module - 1000BASE-T - SFP to RJ45 Cat6/Cat5e - 1GE Gigabit Ethernet SFP - RJ-45 100m

Product ID: 10050-ST



The 10050-ST is an Extreme Networks 10050 compatible copper transceiver module that has been designed, programmed and tested to work with Extreme Networks brand switches and routers. It delivers dependable 1 GbE connectivity over copper cable, for 1000Base-T compliant networks, with a maximum distance of up to 100 m (328 ft).

- 1000 Mbps (1 Gbps)
- Copper
- RJ-45
- 100 m (328 ft)
- 510,469,759 hours
- Low power consumption
- No

This SFP copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

Features

- 100% EXTREME NETWORKS 10050 COMPATIBLE SFP TRANSCEIVER: Designed, programmed and tested to work with compatible Extreme Networks switches and routers to deliver dependable 1GbE connectivity
- TECHNICAL SPECS: 1000BASE-T 1Gbps Copper RJ-45 Connector Distances up to 100m (328ft)

- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Extreme Networks routers and switches
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware	Warranty	Lifetime
	Compatible Brand	Extreme Networks
	Industry Standards	IEEE 802.3 1000BASE-T
Performance	Maximum Data Transfer Rate	1.00 Gbps
	Max Transfer Distance	100 m (328 ft)
	Type	Copper
	Fiber Operating Mode	Full-Duplex
	DDM	No
	Compatible Networks	1000 Mbps (1 Gbps)
	MTBF	510,469,759 hours
	Physical Characteristics	Product Length
Product Width		2.7 in [68 mm]
Product Height		0.5 in [13.8 mm]
Weight of Product		0.5 oz [15 g]
Packaging Information	Package Length	4.5 in [1.2 cm]
	Package Width	3.5 in [90 mm]
	Package Height	1.2 in [31 mm]
	Shipping (Package) Weight	1.8 oz [50 g]
What's in the Box	Included in Package	SFP Transceiver

****Product appearance and specifications are subject to change without notice.***

