

30W USB-C Wall Charger, Portable GaN Charger with USB Power Delivery Fast Charging, GaN 5V/9V/15/20V PD, USB-C Charger, Black

Product ID: 103NB-WALL-CHARGER



This 30W USB-C Power Delivery wall charger delivers fast, efficient charging for the MacBook Neo, iPhones, Android phones, tablets, and other low-power USB-C devices. With a compact GaN design and built-in safeguards, it's ideal for travel, remote work, and everyday charging on the go.

This ultra-compact 2oz charger (35.5 x 30.9 x 27.8 mm) stays cool under load and is easy to pack for mobile professionals and commuters.

Optimized for lower-power USB-C devices, this charger supports fast charging for iPhone Pro/Max, iPhone 17, iPad Pro/Air and Samsung Galaxy. It can provide supplemental charging for laptops, like the MacBook Air, when they are not actively being used, such as overnight or between work sessions. Supports USB PD at 5V, 9V, 15, and 20V.

Built-in protection guards against over-voltage, over-current, and heat. Certified for global use with cULus, FCC/ICES, and Japan PSE certifications.

This charger features a housing made from 75% post-consumer recycled (PCR) material. The product also ships in FSC Mix packaging made from responsibly sourced materials. These materials help align your IT infrastructure with your organization's sustainability goals, without compromising on quality or durability.

Certifications, Reports and Compatibility

Applications

- Enables mobile professionals and hybrid workers to fast-charge phones and tablets in travel, hoteling, or shared workspaces without carrying bulky OEM adapters
- Provides a compact, certified charging solution for enterprise-issued iPhone, iPad, and USB-C devices, supporting

safe deployment in regulated or environmentally conscious organizations

Features

- **Charge Quickly On the Go**: Deliver up to 30W of USB-C Power Delivery at 5V, 9V, 15, or 20V to fast-charge compatible phones, tablets, and accessories when away from desk; For quick charging of supported devices; Not intended to power laptop during active use
- **Pack Light, Power More**: This ultracompact 2oz GaN charger with a 35.5 x 30.9 x 27.8 mm footprint and low 0.6A input current reduces heat and bulk while delivering reliable performance; Ideal for commuters, frequent travelers, and compact workspaces
- **Standardize Charging Across Modern Devices**: Charge the MacBook Neo, USB-C tablets, iPhone Pro and Max, iPhone 17, iPad Pro and Air, and Samsung Galaxy devices from one reliable charger, optimized for lower power hardware
- **Protect Devices with Certified Safety**: Builtin protection guards against overvoltage, overcurrent, and heat; cULus, FCC/ICES, and Japan PSE certified for global safety; Features 75% postconsumer recycled (PCR) housing and FSCMix certified packaging
- **The IT Pro's Choice**: Our power adapters offer a long-lasting, eco-conscious solution as manufacturers increasingly exclude chargers from new devices; Thoroughly tested in our Innovation Lab to ensure enterprise-grade reliability and operational safety

Hardware

Warranty	2 Years
Ports	1

Connector(s)

Input Connector(s)	1 - NEMA 1-15 Power (North America)
Output Connectors	1 - USB Type-C (24 pin) USB Power Delivery Only
	1 - USB Type-C (24 pin) USB Power Delivery Only

Indicators

LED Indicators	1 - Blue
----------------	----------

Power

Input Voltage	110V-240V AC
Input Current	1.0 A
Output Voltage	5V DC
	9V DC

	15V DC
	20V DC
Output Current	3 A
Plug Type	NEMA 1-15 Power (North America) Plug
Power Consumption (In Watts)	30 W
Environmental	
Operating Temperature	0 to 25C (32 to 77F)
Storage Temperature	-20 to 85C (-4 to 185F)
Humidity	20% ~ 90% RH
Physical Characteristics	
Color	Black
Product Length	1.4 in [35.5 mm]
Product Width	1.1 in [27.8 mm]
Product Height	1.2 in [30.9 mm]
Weight of Product	1.6 oz [44 g]
Packaging Information	
Package Length	3.1 in [8.0 cm]
Package Width	3.7 in [9.3 cm]
Package Height	1.5 in [3.8 cm]
Shipping (Package) Weight	2.8 oz [80.0 g]
Warranty Information	
Warranty	2 Years

**Product appearance and specifications are subject to change without notice.*