25ft (7m) DisplayPort Cable - 2560 x 1440p - DisplayPort to DisplayPort Cable - DP to DP Cable for Monitor - DP Video/Display Cord - Latching DP Connectors - HDCP & DPCP

Product ID: DISPLPORT25L

The DISPLPORT25L 25-foot DisplayPort cable provides a connection of up to 25ft between a DisplayPort source and a DisplayPort display, with no loss of signal quality – almost/,more than double the typical DisplayPort connection distance limitation of 16ft. Its 26 gauge (AWG) pure copper wire, and Aluminum and Mylar shielding helps to eliminate EMI and RFI interference.Delivering a maximum bandwidth of 10.8 Gbps, the DISPLPORT25L is capable of providing higher performance than either HDMI or dual link DVI and supporting next generation multimedia applications with a maximum resolution capability of up to WQXGA (25601600).

The DisplayPort cable's small, USB-sized latching connectors support two-way display connectivity and optional audio support.

The DISPLPORT25L DisplayPort cable is both HDCP and DPCP capable, ensuring that digitally protected content is displayed properly on the connected display.

Certifications, Reports and Compatibility

RoHS Compliant

Applications

• Connecting a DisplayPort display to a PC or alternative DisplayPort source

Features

• HIGH PERFORMANCE CABLE: This 25ft (7m) DisplayPort to DisplayPort cable supports 2K (2560x1440p) 30Hz, Full HD (1920x1200p) 60Hz, 10.8 Gbps bandwidth, Multi-Stream Transport (MST), 5.1, 7.1 Audio Channel, GTC for precise audio channel timing & 3D Stereo

• RELIABLE DESIGN: Durable ABS connectors with flexible PVC strain relief & jacket prevents fraying/damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding; Latching DP connectors prevent accidental disconnection

• QUALITY CONSTRUCTION: 26AWG wire with gold-plated connectors for improved signal integrity and reliability; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio; Backwards compatible with DP 1.1

• APPLICATIONS: Ideal for home/offices/boardrooms/conference rooms/classrooms; works with your professional workstations with FirePro S9000/7000, W8100/7100/5100 or R5000 graphic cards; Use with 1080p/UHD/4K monitors, projector or large display

• SPECS: 25 ft (7 m) Black DisplayPort v1.0 DP Latching Male to Male 26 AWG PVC cable jacket, ABS connector shell Shield: Al-Mylar foil with Braid Protocols: MST, GTC Lifetime Warranty

Hardware		
	Warranty	Lifetime
	Number of Conductors	19
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
	Fire Rating	CMG Rated (General Purpose)
Connector(s)		
	Connector A	1 - DisplayPort (20 pin)
	Connector B	1 - DisplayPort (20 pin)
Physical Characteristics		
	Color	Black
	Connector Style	Latching
	Wire Gauge	26 AWG (0.404 mm)
	Cable Length	25.0 ft [7.6 m]
	Cable OD	0.3 in [8.5 mm]

	Product Length	25.0 ft [7.6 m]
	Product Width	0.8 in [2.1 cm]
	Product Height	0.5 in [1.4 cm]
	Weight of Product	1.2 lb [0.6 kg]
Packaging Information		
	Package Quantity	1
	Package Length	13.0 in [33.0 cm]
	Package Width	9.9 in [25.2 cm]
	Package Height	1.6 in [4.0 cm]
	Shipping (Package) Weight	1.3 lb [0.6 kg]
What's in the Box		
	Included in Package	1 - 25 ft DisplayPort Cable with Latches - M/M

Product appearance and specifications are subject to change without notice.