6in DisplayPort Port Saver Cable – M/F

Productcode: DPEXTAA6IN

The DPEXTAA6IN 6-inch DisplayPort Port Saver Cable/coupler avoids expensive repairs to a computer or display. It does this by extending the port by 6in, thereby eliminating the weight and stress that would typically be placed on the port by a DisplayPort cable. This is especially useful in an environment where cables are unplugged and re-inserted frequently.

Certificaties, rapporten en compatibiliteit

RoHS Compliant

Toepassingen

• Protect the on-board DisplayPort interface from damage cause by frequent connect/disconnects

• Allows supported Displayport devices to draw power from the host device

Eigenschappen

• Molded latching connectors with strain relief

• Includes all 20 DisplayPort pins to support Multi-Mode DisplayPort devices

• Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP

Hardware		
	Garantiebeleid	Lifetime
	Aantal geleiders	20
	Connectormateriaal	Goud
	Type kabelmantel	PVC - Polyvinyl Chloride
	Kabelafscherming	Aluminium-Mylar folie met vlechtwerk
Connector(en)		
	Connector A	1 - DisplayPort (20-polig)
	Connector B	1 - DisplayPort (20-polig)
Fysieke eigenschappen		
	Kleur	Zwart
	Draaddikte	28 AWG
	Max. afmeting connector	0.8 in [20.4 mm]
	Kabellengte	6.0 in [152.4 mm]
	Buitendiameter kabel	0.3 in [7.3 mm]
	Gewicht product	1.3 oz [38 g]
Verpakkingsinformatie		
	Verpakkingsaantal	1
	Package Length	4.7 in [11.9 cm]
	Package Width	0.7 in [19 mm]
	Package Height	8.4 in [21.3 cm]
	Verzendgewicht (verpakt)	2.5 oz [70 g]
Wat wordt er meegeleverd		

Meegeleverd	1 - 6in DisplayPort port extension

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.