

140W USB-C Wall Charger, USB-IF Certified, Single USB-C, PD 3.1 Portable GaN Charging, Power Adapter for MacBook M3 Pro/Max, Dell XPS/Inspiron/Precision

Product ID: 1014GCN-WALL-CHARGER



This USB-IF Certified 140W USB-C GaN Charger delivers a versatile, high-power charging solution for USB-C devices, supporting up to 140W with PD 3.1. The package includes a 6 ft (1.8 m) USB-C cable, so you have everything needed for immediate, reliable charging.

The USB-IF Certified Power Adapter and included USB-IF Certified USB Type-C cable provide safe and reliable charging solutions. Supporting high-performance USB Power Delivery (PD) 3.1 with Extended Power Range (EPR), this adapter can charge demanding 140W devices, including the MacBook M3 Pro/Max. Its robust design accommodates current laptops like the MacBook Air, Dell XPS, iPad Pro, iPhone, Samsung smartphones, and Google Pixel, while also ensuring future-proof compatibility with next-generation devices.

This USB Wall Charger is engineered for optimal cooling, providing a safer, more reliable charging experience. Balancing compact size with powerful functionality, it features a foldable North American power plug (NEMA 1-15P) for easy storage and delivers fast, efficient charging while maintaining long-lasting performance. At just 10.5 oz (299 g), this travel-friendly adapter combines robust capabilities with easy portability, making it an ideal companion on the go.

Safety and efficiency are paramount with the 140W USB GaN Charger. It is TUV Safety Listed (IEC 62368-1) and FCC/ICES EMC certified, providing protection against over-voltage, current, and temperature. The Active Power Factor Correction (PF > 0.99) enhances efficiency and ensures cool operation. Additionally, it meets DOE Level VI standards, guaranteeing energy efficiency and reliable performance.

Certifications, Reports and Compatibility



Applications

- Ideal for travel with a light weight design and port variation eliminating the need to carry multiple chargers for different devices
- Power laptops and other USB devices in at the office or home office

Features

- **140W USB GaN CHARGER:** USB wall charger with 1x USB-C (140W max, PD 3.1); Compact travel adapter (10.5 oz/299 g); Charges with multiple PD voltage profiles (5V/9V/12V/15V/20V/28V at up to 5A); 6ft (1.8m) 240W EPR USB-IF Certified USB Type-C Cable Included
- **USB-IF CERTIFIED & EPR READY:** Power Adapter and included USB-C Cable are USB-IF certified for safe & reliable charging; Supports high-performance PD 3.1 with EPR for charging 140W devices like MacBook M3 Pro/Max; Future-proof for next-gen laptops
- **16" MACBOOK PRO COMPATIBLE:** PD 3.1 Power Adapter fully supports MacBook M3 Pro/Max ensuring high-speed 140W charging; Charges all USB-C devices with earlier PD revisions like MacBook, Dell XPS/Precision/Inspiron, iPad Pro, iPhone & Samsung smartphones
- **COMPACT & COOL RUNNING:** Engineered for cool performance under extended full-load use, with a foldable North American power plug (NEMA 1-15P) that enhances portability and easy storage; Small footprint (2.6 in/6.8cm x 1.2in/3.1cm x 3in/7.8cm)
- **SAFE, RELIABLE & EFFICIENT:** Designed to keep users & devices safe; TUV Safety Listed (IEC 62368-1) & FCC/ICES EMC certified; Over-voltage, current, and temp. protection; Active Power Factor Correction (PF > 0.99); Meets DOE Level VI standards

Hardware

Warranty	2 Years
Number of Power Outlets	1
Industry Standards	USB Power Delivery 3.1

Connector(s)

Input Connector(s)	1 - NEMA 1-15 Power (North America)
Output Connectors	1 - USB Type-C (24 pin) USB Power Delivery Only

Power

Input Voltage	100 - 240 AC
Input Current	2.0A
Output Voltage	15V DC

	5V DC
	9V DC
	12V DC
	20V DC
	28V DC
Output Current	3A (5V, 9V, 12V, 15) / 5A (20V, 28V)
Plug Type	NEMA 1-15 Power (North America) Plug
Power Consumption (In Watts)	140 W

Environmental

Operating Temperature	0 to 25C (32 to 77F)
Storage Temperature	-20 to 80C (-4 to 176F)
Humidity	Operation: 10% ~ 90% RH Storage: 30% ~ 90% RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	2.7 in [6.8 cm]
Product Width	1.2 in [3.1 cm]
Product Height	3.1 in [7.8 cm]
Weight of Product	10.6 oz [299.0 g]

Packaging Information

Package Length	3.3 in [8.3 cm]
Package Width	6.3 in [16.0 cm]
Package Height	1.4 in [3.5 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

What's in the Box

Included in Package	1 - USB Wall Charger
	1 - 6 ft. [1.8m] USB-C Cable (240W)
	1 - Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***