Fiber Optic Cable - Multimode Duplex 62.5/125 - LSZH - LC/ST - 3 m

Produkt ID: FIBLCST3



The FIBLCST3 3-meter (10ft) Multimode 62.5/125 Duplex Fiber Patch Cable is terminated with one LC (male) connector and one ST (male) connector, to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

This LC-ST patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

To ensure optimum performance, our multimode fiber duplex cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Backed by Lifetime Warranty, our LC-ST Multimode Fiber Patch cable is guaranteed to provide long-lasting dependability, and top quality performance.

Certifikat, rapporter och kompatibilitet

RoHS Compliant

Användning

• Ideal solution for data applications requiring high speed data transmission

• Broadband systems

- Telecommunication/Data communication
- Used by long distance networks with mission critical data

Funktioner

- Attenuation loss meets or exceeds industry standards
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Immune to electrical interference

Hårdvara		
	Garantipolicy	Lifetime
	Brandteknisk klass	LSZH-klassad (Low Smoke Zero Halogen)
	Fiberstorlek	62.5/125
Prestanda		
	Maximal dataöverföringshastighet	10Gbps
	Kabelklassificering	1Gbps / 10Gbps
	Fiberklassificering	OM1
	Fibertyp	Multiläge
Kontakt(er)		
	Connector A	1 - Fiberoptisk LC duplex
	Connector B	1 - Fiberoptisk ST duplex
Miljö		
	Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
	Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
	Luftfuktighet	0~90% RH
Utseende		

	Färg	Orange
	Kabellängd	9.8 ft [3 m]
	Produktlängd	9.8 ft [3.0 m]
	Produktbredd	0.5 in [1.2 cm]
	Produkthöjd	0.3 in [0.7 cm]
	Produktvikt	1.8 oz [52.0 g]
Förpackning		
	Förpackningsantal	1
	Package Length	8.7 in [22.0 cm]
	Package Width	7.9 in [20.0 cm]
	Package Height	0.8 in [2.0 cm]
	Fraktvikt (förpackning)	2.2 oz [61.0 g]
Vad det är i lådan		
	Ingår i paketet	1 - 3m Multimode 62.5/125 Duplex Fiber Patch Cable LC – ST

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.